



DLE220

Leading Edge Dimmer Controller

Designed for applications where lamp life is critical


The Philips Dynalite DLE220 is a two-channel leading edge dimmer controller, with a maximum load of 20 A per channel. It is suitable for use with incandescent, neon and selected fluorescent light sources, as well as iron core and leading edge dimmable electronic transformers.


DLE220

Designed for applications where lamp life is critical

- Large load capability Complements multichannel dimmers by providing extra channels where additional capacity is required.
- Reliable control Suitable for applications where lamp life is critical, such as where lamp replacement is difficult or expensive.
- Interference suppression Iron powder core toroidal choke lessens effects of interference from other equipment, such as transformers.
- Naturally ventilated Requires no forced cooling or maintenance.
- Soft start and voltage regulation technologies –
 Protects lamps from over voltage and dramatically
 improves lamp life, reducing maintenance costs.
- Diagnostic functionality Device Online/ Offline status reporting.
- User controls Incorporates service override switch all channels to 100% and a diagnostic LED.

Dimensions





Specifications

Due to continuous improvements and innovations, specifications may change without notice.



DLE220

Leading Edge Dimmer Controller

Electrical

Electrical	
Supply Type	Single-phase
Supply Voltage	230 VAC (±14%)
Supply Current	40 A
Backup CPU Supply	12 VDC @ 1 A (SELV / Class 2)
Outputs	2 x Leading edge dimming
Output Channel Rating	≤ 20 A
Total Box Load	≤ 40 A
DyNet DC Output Voltage	12 VDC
DyNet DC Output Current	200 mA
Power Conditioning	Regulated outputs Overvoltage protection Surge protection Brownout / Sag protection Spike protection Soft start 16 bit fade resolution (65,536 steps)
Electrical Protection	2 x 20 A circuit breakers (single-pole thermal magnetic, 6 kA surge)
Regulating Device	2 x SCR (65 A nom., 800 V, 800 A surge)
Interference Suppression	Iron powder toroidal choke
Rise Time	200 μS
IEC Overvoltage Category	III
Control	
Serial Ports	1 x RS485
Supported Protocols	DyNot

Control	
Serial Ports	1 x RS485
Supported Protocols	DyNet DMX Rx
DMX Rx Channels	2
Dry Contact Inputs	1 (AUX)
Diagnostic Functions	Device online/offline status
User Controls	1 x service switch 2 x output channel override
Indicators	1 x service LED

Physical

Dimensions (H x W x D)	325 x 212 x 178 mm (12.79 x 8.35 x 7.01 in)
Packed Weight	4.2 kg (9.26 lb)
Construction	Alloy/steel wall mount case Powder coat finish
Mains Cable Entry	3 x Ø 25 mm knockout
Data Cable Entry	1 x Ø 25 mm knockout
Serial Ports	1 x RJ12 1 x 6-way screw terminal
Serial Port Conductor Size	2.5 mm ² (#12 AWG) (max)
Supply Terminals	2 x screw terminal (Line, Neutral)
Supply Terminal Conductor Size	10 mm² (#6 AWG) (max)
Load Terminals	4 x screw terminal
Load Terminal Conductor Size	5 mm² (#10 AWG) (max)
Earth Bar Terminals	5 x screw terminal
Earth Bar Terminal Conductor Si	ze 1 x 16 mm² (#6 AWG) (max) 4 x 5mm² (#10 AWG) (max)

Environment*

Operating Temperature	0° to 40°C ambient (32° to 104°F)
Storage/Transport Temperature	-25° to 70°C ambient (-13° to 158°F)
Humidity	0 to 90% non-condensing
IEC Pollution Degree	II


Compliance

Certification CE, RCM, UKCA, F	₹oHS
--------------------------------	------

^{*} For indoor installation only



Electrical



Ordering Code

Product	Philips 12NC
DLE220 (Standard)	913703002009



© 2021 Signify Holding. All rights reserved. Specifications are subject to change without notice. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

Revision 06 2021-09-09 lighting.philips.com/dynalite