






Project:
Spec Type:
Catalog No: 3908LxGQ
Qty
Line Notes:

TruGroove recessed delivers unrivaled performance and a truly innovative design – making a definitive statement in any architectural space. TruGroove recessed corners provide endless opportunities for creative freedom with geometric patterns in walls and ceilings.

## **Ordering guide**



- \* Nominal values within a range. Consult photometry data for CRI, color temp, lumens & distribution of chosen configuration.
- † Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options
- ≈ Available in continuous run lengths from 6ft in steps as small as 1/8in for 1500lm/4ft & 2200lm/4ft symmetric configurations.
- ≈ All 3000lm/4ft, 4000lm/4ft and asymmetric configurations can be specified in 1ft steps.

## **Ceiling Trims** Integrated Controls Please indicate with check mark. Response Daylight Single Zone (DS) T-Grid **Drywall Trimless** Drywall Trim







# Asymmetric MesoOptics Lens 2200 lm/4ft, 3000/3500/4000K

## **Optical System**

Performance version: White light emitted from the LED sources is internally reflected and exits through the optical lens assembly. This assembly contains acrylic extrusion profiles to retain a layer of MesoOptics film, creating both an uninterrupted continuum of light and an optical batwing distribution.

**Definition version**: Light passes through a diffuse white acrylic lens to deliver a highly uniform luminous continuum.

#### **Finish**

Extruded aluminum trim and die-cast endplates coated with electrostatically applied and thermally cured polyester. Powder coat paint finish. White sensors only.

#### Housing

Die-formed 20 gauge cold-rolled steel. Multiple upper wire entrances available for continuous row mounting of fixtures

#### Weight

Maximum 3.5lb/ft.

#### **Electrical**

Factory pre-wired to section ends with quick-wire connectors.

#### **Wall Options**

Wall mounted luminaires are only available with the Drywall Trimless ceiling / trim option. A continuous ceiling to wall pattern with an inside corner can use a different ceiling / trim option on the ceiling if required.

Regressed lens and 4000 lm/4ft configurations are not available for wall mounting.

#### Standard Drivers

Philips Advance Xitanium 0-10V, 1-100%. Philips Advance Xitanium Sensor Ready, 5-100%. Class 2 rated output. Consult Philips Ledalite for other available drivers.

### **Standard Battery Pack**

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output: 1100lm.

#### **Lumen Maintenance**

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C in non-insulated contact applications the LED lumen maintenance expectation according to IES TM-21-11 is:

L<sub>90</sub> (10k) >60,000 hrs (**Reported** methodology) L<sub>80</sub> (10k) 120,000 hrs (**Calculated** methodology).

#### **Source Color**

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 2 SDCM.

#### Controls

Certain configurations available with: Response Daylight Sensors SpaceWise DT Occupancy & Daylight Sensors w/ advanced grouping & Dwell Time.

\*SpaceWise DT commissioning is via a compatible Android phone and Philips Field App. Compatible wireless dimming wall switches are available for dimming. 347V is not available as a standard option. For more information, please refer to www.philips.com/spacewise

### Mounting

Mounting brackets on housing sides support T-Grid installation. 1/16" diameter aircraft cable with self-locking, tamper-resistant, miniature cable gripper provides vertical adjustment for drywall. Aircraft cable, crimp and gripper independently tested to meet stringent safety requirements.

Compatible with 4" Armstrong TechZone ceiling grid.

#### Joints

Self-aligning joining system with hands-free pre-joining wire access

### **Approvals**

Certified to UL, CSA and IES standards. Insulation Contact (IC) rated. Most symmetric, flush lens versions between 1500-3000lm/4ft in 3500K and 4000K are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers under DLC family code WWWBXQ (www.designlights.org/QPL).

#### Warranty

Five-year luminaire limited warranty including LED boards and driver.

USA: http://www.usa.lighting.philips.com/support/support/warranty


Canada: http://www.lighting.philips.ca/support/support/warranty


#### **Environment**

Rated for dry & damp locations in operating in ambient temperatures of 25°C. Many luminaire components, such as reflectors, refractors, lenses, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility. Damage caused by sulfur, chlorine, petroleum based solution or other contaminants are not covered under warranty


 $\label{eq:decomposition} Due to continuing product improvements, Phillips Ledalite reserves the right to change the specifications without notice.$ 

## Corner details and dimensions






O\	verall Trim ————	<u>H</u>				
ominal ength	Housing	Lens	Mounting Points	Trim - T-Grid	Trim - Drywall Trimless	Trim – Drywall Trim
2ft Flat	25.7"/653mm	N/A	23.6"/600mm	25.9"/658mm	27.1"/689mm	26.3"/667mm



Nominal Length	Trim-Drywall Trimless	
2x2ft Outside	26.8"/681mm	


Asymmetric MesoOptics Lens 2200 lm/4ft, 3000/3500/4000K


## **Ceiling Types**



## Module Details & Dimensions


## Standalone






Standalone								
Nominal	Housing	Lens	Mounting Points	Trim -T-Grid	Trim - Drywall Trimless	Trim - Drywa <b>ll</b> Trim		
2ft	23.9~/607mm	23.0″/584mm	23.4"/594mm	23.8"/605mm	26.4"/670mm	24.5"/622mm		
3ft	35.9"/912mm	35.0"/889mm	35.4"/899mm	35.8"/909mm	38.4"/975mm	36.5"/927mm		
4ft	47.9"/1217mm	47.0°/1194mm	47.4"/1204mm	47.8"/1214mm	50.4″/1280mm	48.5"/1232mm		
5ft	59.9"/1521mm	59.0~/1499mm	59.4″/1509mm	59.8"/1519mm	62.4"/1585mm	60.5″/1537mm		
6ft	71.9"/1826mm	71.0°/1803mm	71.4"/1814mm	71.8"/1824mm	74.4"/1889mm	72.5"/1841mm		
8ft	95.9"/2436mm	95.0"/2413mm	95.4″/2423mm	95.8"/2433mm	98.4"/2499mm	96.5″/2451mm		


## Mid-Run



Mid-Run	Mid-Run							
Nominal	Housing & Lens	Mounting Points						
2ft	24.0~/610mm	23.2"/589mm						
3ft	36.0°/914mm	35.2"/894mm						
4ft	48.0"/1219mm	47.2"/1199mm						
5ft	60.0"/1524mm	59.2°/1504mm						
6ft	72.0"/1829mm	71.2"/1809mm						
8ft	96.0"/2438mm	95.2"/2418mm						
Incremental	L	L-0.8"						

## End-Run






End-Run	End-Run									
Nominal Housing		Lens Mounting Points		Trim -T-Grid	Trim - Drywall Trimless	Trim - Drywall Trim				
2ft	24.0°/610mm	23.5"/597mm	23.2*/589mm	23.9″/606mm	25.7"/653mm	24.8"/629mm				
3ft	36.0°/914mm	35.5"/901mm	35.2"/894mm	35.9°/910mm	37.7″/957mm	36.7"/933mm				
4ft	48.0~/1219mm	47.5"/1206mm	47.2"/1199mm	47.9~/1215mm	49.7″/1262mm	48.7"/1238mm				
5ft	60.0"/1524mm	59.5"/1511mm	59.2"/1504mm	59.9″/1520mm	61.7"/1567mm	60.7″/1543mm				
6ft	72.0"/1829mm	71.5~/1816mm	71.2"/1809mm	71.9"/1825mm	73.7"/1872mm	72.8"/1848mm				
8ft	96.0″/2438mm	95.5"/2425mm	95.2"/2418mm	95.8"/2434mm	97.7″/2481mm	96.7″/2457mm				
Incremental	L	L-0.5"	L-0.8"	L-0.1"	L+1.7"	L+0.75"				

Asymmetric MesoOptics Lens 2200 lm/4ft, 3000/3500/4000K

## Photometry @ CRI>80, 3500K





All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies

4500K

Visit www.lightingfacts.com for the Label Reference Guide.

Bright White

Registration Number: F46Z-74EX5T (10/31/2017) Model Number: 39x8LBGQxx04 Type: Luminaire - Linear

3000K

2700K

### Candela Distribution

Vertical	Horizontal Angle					Zona
Angle	0	45	90	135	180	Lumen
0	902	902	902	902	902	0
5	1039	1002	868	788	728	85
15	1253	1148	821	614	563	246
25	1170	1103	718	501	461	360
35	842	812	585	404	377	373
45	488	495	406	303	284	307
55	295	295	259	214	200	228
65	170	167	157	138	128	152
75	78	74	75	70	63	78
85	20	18	19	21	18	22
90	0	0	0	0	0	0
95	0	0	0	0	0	0
105	0	0	0	0	0	0
115	0	0	0	0	0	0
125	0	0	0	0	0	0
135	0	0	0	0	0	0
145	0	0	0	0	0	0
155	0	0	0	0	0	0
165	0	0	0	0	0	0
175	0	0	0	0	0	0
180	0	0	0	0	0	0

Values per 4ft unit

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

## Coefficients of Utilization (%)

DCD	Ceiling:		8	0			70			50		0
RCR	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		119	119	119	119	116	116	116	111	111	111	100
1		110	106	102	99	108	104	100	100	97	94	87
2		102	94	88	83	99	92	87	89	84	80	75
3		94	84	77	71	91	83	76	80	74	69	65
4		87	76	68	62	84	74	67	72	66	61	57
5		80	69	60	54	78	67	60	65	59	54	50
6		75	62	54	48	73	61	54	60	53	48	45
7		70	57	49	43	68	56	49	55	48	43	40
8		65	53	45	39	64	52	44	51	44	39	37
9		61	49	41	36	60	48	41	47	40	35	33
10		57	45	38	33	56	45	37	44	37	33	31

## Avg. Luminance (cd/m2)

Vertical	H	orizontal Ang	gle
Angle	0	90	180
55	5542	4850	3752
65	4333	3995	3247
75	3229	3103	2636
85	2508	2366	2259

## Distribution

Philips Ledalite

6500K

Hemisphere	0% Up / 100% Down
Glare Control	Meets RP-1-12 recommendations for VDT-Critical spaces
Spacing Along (0°)	1.41
Spacing Across (90°)	1.11
Spacing at 180°	0.66

Asymmetric MesoOptics Lens 2200 lm/4ft, 3000/3500/4000K

## **Optical Performance @ 120V**

Nominal Spec:	830	835	840
Flux (lm)	1784	1851	1858
Efficacy (lm/W)	87.0	90.3	91.1
Power (W)	20.5	20.5	20.4
CCT (K)	3040	3437	3948
CRI	84	82	84
R9	16	10	14
x	0.4334	0.4097	0.3836
У	0.4017	0.3945	0.3813
Duv	0.0006	0.0007	0.0013

## Electrical Performance @ CRI>80, 3500K

Input Voltage	120V	277V	347V
Input Power	20.5W	20.9VV	20.7W
Input Current	0.17A	0.08A	0.06A
Power Factor	0.988	0.924	0.970
Total Harm. Distortion	13.0%	17.6%	11.5%

Tested values – contact technical support for rated values. Off-state power zero unless certain controls are specified.

