


With its slim, uncluttered design, Sync is the epitome of compact style. Sync offers true direct/indirect lighting distribution and luminous aesthetics with exceptional glare control.

## Ordering guide



# Mount Type Consult separate mounting spec sheet for mount type options Endcaps - Integrated Controls Please indicate with check mark. Response Daylight Single Zone (DS)







<sup>\*</sup> Nominal values within a range. Down kits reduce output & efficacy. Consult photometry data for color temp, lumens & distribution of chosen configuration.

<sup>†</sup> Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

# 3400 lm/4ft 75% Up 3000/3500/4000K

#### **Optical System**

The optical system contains arrays of LEDs edge-lighting a low profile light-guide panel, using total internal reflection to homogenize the sources. The microstructured surface of the panel optimizes light extraction to create an efficacious direct/indirect distribution. Light is purified and controlled by MesoOptics film as it passes through a non-glare acrylic lens. Standard distribution is 75% up / 25% down for suspended and 65% up / 35% down for wall mount version.

#### **Endcaps**

Diecast aluminum endcaps, available in flat (standard) or sculpted (optional).

#### **Finish**

Standard finish is a textured matte powder coat in white, black or titanium silver.

#### Housing

Precision formed 18 gauge cold-rolled steel.

#### Weight

Maximum: Suspended 3.75lb/ft & Wall 3.0lb/ft.

#### Electrical

Factory pre-wired to section ends with quick-wire connectors.

#### **Standard Driver**

Philips Advance Xitanium 0-10V, 1-100%. Class 2 rated output. Consult Philips Ledalite for other available drivers.

#### **Standard Battery Pack**

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output: 1100lm.

#### **Lumen Maintenance**

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 is: L<sub>80</sub> (12k) >72,000 hrs (Reported methodology).

#### **Source Color**

LEDs rated for color rendering CRI >80 and fixture to fixture color accuracy within 2 SDCM.

#### **Controls**

Suspended version available with the following integrated controls: Response daylight sensor (for single zone).

#### Mounting

Suspended: Tamper-resistant aircraft cable gripper provides unlimited vertical adjustment. Aircraft cable, crimp and cable gripper are independently tested to meet stringent safety requirements.

**Wall**: Fixture is mounted flush to wall using hidden wall brackets which attach to existing structure, variable within 2"-5" of end or joint.

#### Joints

Self-aligning joining system with hands-free pre-joining wire access

#### **Approvals**

Certified to UL, CSA and IES standards.
Certain suspended versions without down kits are
DesignLights Consortium® qualified. Please see the DLC
QPL list for exact catalog numbers
(www.designlights.org/QPL).

#### Warranty


Philips indoor professional luminaires 5 year LED warranty: www.philips.com/warranties.

#### **Environment**

Rated for dry or damp locations in operating ambient temperatures 0–40°C (32–104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants are not covered under warranty. Not suitable for natatorium environments.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.

#### **Dimensions - Cross Section**



3400 lm/4ft 75% Up 3000/3500/4000K

# **Dimensions - Modules**


## Modules

Module length excludes end caps. Nominal mounting spacing for individually mounted modules.

	← 4' (1219.2mm) — →	
4 ft.		
	<b>├</b> 8' (2438.8	mm) ———————————————————————————————————
8 ft		


Note: Refer to installation instructions for exact mount.

# **Optics and Styles**




3400 lm/4ft 75% Up 3000/3500/4000K

#### Photometry - 3500K



75% Up / 25% Down



#### Candela Distribution

Vertical Angle	0	Hori 22.5	zontal A	Angle 67.5	90	Zonal Lumens
O O	229	229	229	229	229	
5	230	231	233	236	236	23
15	244	250	269	288	295	77
25					378	147
35	261 259	276	320	361		
		274	315	350	363	193
45	206	210	221	229	232	170
55	137	135	136	140	142	124
65	81	80	82	85	88	82
75	33	34	35	36	36	38
85	6	7	7	7	8	9
90	0	0	0	0	0	0
95	99	115	162	226	252	180
105	259	308	458	665	767	502
115	341	397	556	761	862	567
125	350	394	510	645	708	465
135	330	363	422	490	519	331
145	316	338	365	394	406	230
155	309	324	343	352	353	157
165	304	313	323	329	330	91
175	300	303	305	307	308	29
180	299	299	299	299	299	0
	1 -//	-//	-//	-//	-//	,

Values per 4ft unit

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

## Coefficients of Utilization (%)

0.00	Ceiling:		8	0			70			50		0
RCR	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		101	101	101	101	90	90	90	70	70	70	25
1		92	88	85	81	82	79	76	61	59	57	22
2		84	77	71	67	75	69	64	54	50	48	18
3		77	68	61	56	68	61	55	47	43	40	16
4		70	60	53	47	62	54	47	42	38	34	13
5		64	53	46	40	57	48	41	37	33	29	12
6		59	48	40	34	52	43	36	34	29	25	10
7		54	43	35	30	48	38	32	30	26	22	9
8		50	39	31	26	45	35	28	27	23	19	8
9		47	35	28	23	42	32	25	25	20	17	7
10		44	32	25	20	39	29	23	23	18	15	6

#### Avg. Luminance (cd/m2)

Vertical	Ho	orizontal An	gle
Angle	0	45	90
55	2318	2301	2402
65	1860	1883	2020
75	1237	1312	1350
85	668	779	891

## **Distribution**

Hemisphere	75% Up / 25% Down
Peak/Zenith	2.91
Peak Output	869 cd
Glare Control	Meets RP-1-12 recommendations for VDT-Critical spaces

3400 lm/4ft 75% Up 3000/3500/4000K

## **Optical Performance**

Nominal CCT:	3000K	3500K	4000K	
Flux (lm)	3271	3416	3513	
Efficacy (lm/W)	114.8	120.3	124.1	
Power (W)	28.5	28.4	28.3	
CCT (K)	3045	3312	3931	
CRI	84	82	83	
R9	10	-1	5	
x	0.4338	0.4167	0.3849	
у	0.4031	0.3968	0.3837	
Duv	0.0000	0.0000	0.0020	

#### **Electrical Performance - 3500K**

Input Voltage	120V	277V	347V
Input Power	28.4W	28.4W	28.5W
Input Current	0.24A	0.11A	0.09A
Power Factor	0.994	0.962	0.953
Total Harm. Distortion	8.0%	11.6%	11.0%

Tested values . contact technical support for rated values. Off-state power zero unless certain controls are specified.

