

Urban

Anchor base post


314- Pole


Project:
Location:

Cat.No:

Type:
Lamps: Qty:

Notes:





Ordering Guide

Example: 314- 8 ABS B B D

Product Code	314-	Anchor Base		
		Post		
Height(s)	8	(8 ft.)		
	10	(10 ft.)		
	12	(12 ft.)		
	14	(14 ft.)		
Finish	ABS	Antique Brass		
	ACP	Antique Copper		
	ARD	Antique Red		
	ASI	Antique Silver		
	BLK	Black		
	BRN	Brown		
	BRZ	Bronze		
	FGN	Forest Green		
	GRA	Granite		
	IRN	Ironstone		
	RBZ	Rustic Bronze		
	SRT	Shadow Rust		
	VBZ	Verde Bronze		
	VCP	Verde Copper		
	VGN	Verde		
	VTC	Vintage Copper		
	WBZ	Weathered		
		Bronze		
	WHT	White		
Photoeye (Optional)	В	120V		
, , ,	С	208V - 277V		
Outlet Location (Optional)	В	4" from Top of		
, , ,		Base		
	Т	12" from Top of		
		Pole		
Outlet Options (Optional)	D	Standard Duplex		
, (),	G	GFI Duplex		

Specifications

OUTLET:

GFI Duplex Outlet has dual-function indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant.

CONSTRUCTION:

Fluted cast aluminum anchor base. Cast aluminum removable access door. Tapered post welded to base. Cast aluminum anchor bolt covers included with post.

FINISH

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

WARRANTY:

Three-year limited warranty.

Tenon/Top:

3" O.D.

314- Anchor base post

Pole

Specifications

Bolt Circle:

9 7/8" dia.

Anchor Rods:

(4) 1/2" dia. x 18" long zinc plated steel

Base Dimensions:

8 1/2" sq. x 32 5/8"

Shaft:

4" to 3" Straight

Wall Thickness:

.125"

Height:

8', 10', 12', 14'

Pole EPA Values

Height

Windspeed(mph)	8'	10'	12'	14'
80	23.1500	16.2500	12.1700	9.4200
110	11.8300	8.0300	5.7100	4.1000
130	7.3700	5.0500	3.3600	2.0200

