

GreenSpace Accent Elbow


Installation instructions

Instructions de montage
Montageanleitung
Montage instructie
Istruzioni di montaggio



Instrucciones de montaje
Instruções de montagem
Monteringsinstruktioner
Monteringsvejledning

Kokoonpano- ja kiinnitysohjeet
Montaj yönergeleri
Odghiez synarmologhshz
Instrukcja montazu

Szerelési utasítás
Návod k montáži
Инструкция по монтажу
Návod k montáži







Type	IP20	GLOW WIRE 650°C	kg	min	max	P _{nom}	P _{max}	Beam angle	
								MB	WB
RS342B LED17S/CRW	•	•	1,25	10°C	40°C	22W	23,5W	•	•
RS342B LED27S/CRW	•	•	1,25	10°C	40°C	35W	37,5W	•	•
RS342B LED39S/CRW	•	•	1,25	10°C	40°C	49W	52W	•	•




1.

444316008031
Version date: 19/01/2015
Data Subject to change without notice
Printed in EU
www.philips.com/lighting

PHILIPS




Optical unit changing and cleaning instructions





2.

Only with soft cloths!




Wiring guide


1, Remove screw and cap




2, Connect L,N



Mains cable



~220-240V



LED17S PSE-E Xitanium 25W 0.3-1A 36V I 230V		LED27S PSE-E Xitanium 36W LH 0.3-1A 48V I 230V		LED39S PSE-E Xitanium 50W 0.7-1.5A 48V TD/I LH140	
Inom(A)	0,093	Inom(A)	0,151	Inom(A)	0,222
I max(A)	8	I max(A)	20	I max(A)	5,3
Tref(ms)	0,18	Tref(ms)	0,25	Tref(ms)	0,7
MCB	Max Products*	MCB	Max Products*	MCB	Max Products*
B-10A	15	B-10A	20	B-10A	18
B-16A	24	B-16A	32	B-16A	30
C-10A	24	C-10A	33	C-10A	31
C-16A	40	C-16A	54	C-16A	51

3.

* According to IEC60555 test conditions