



Project:						
Location:						
Cat.No:						
Туре:						
Lamps:	Qty:					
Notoo:						

Example: K2A244F32G3AP31-1/4-EB

The Day-Brite / CFI Kleenseal KTR 200 recessed is a hosedown cleanroom luminaire well suited for laboratories or food processing areas.

### **Ordering guide**

Family		Size	No. of Lamps	Lamp Type	Ceiling Type	Door Frame	Lens Type	Voltage	No. of Ballasts	Ballast Type	Options
K2A								_	_	_	
K2A Kleen KTR2	00	14 1x4 22 2x2 24 2x4	2 Two lamps 3 Three lamp 4 Four lamps (2x2,2x4) 6 Six lamps (2X4)		G 1",1-1/2" Grid T 2G 2" Grid T F Flange	3 CRS 1-piece overlap white 5 304 1-piece overlap stainless 6 Aluminum 4-piece flush white	AP3 .125" Acrylic Prismatic VPL Sealed Louver Other lenses available	U Universal voltage, 120-277V 1 120V 2 277V 3 347V	1/2 One 2-lamp ballast 2/1 Two 1-lamp ballasts 1/3 One 3-lamp ballast 1/21 2-lamp & 1-lamp ballasts 1/4 One 4-lamp ballast 2/2 Two 2-lamp ballast 2/3 Two 3-lamp ballasts 1/42 4-lamp & 2-lamp ballasts	EB Electronic ballast <10% THD EBIOR T8 electronic ballast, program rapid start, <10% THD	GMF TP Fusing, slow blow Tamper Resistant Screws E7 B60 emerg, ballast, T8, 600- 700 lumens, 120/277V E5 B50 emerg, ballast, U.S. or Canada market, T8, 1100-1400 lumens, UNV DN Lens Furnished Prisms Down SSH Stainless Steel housing RM Row mounting

# **Product Availability**

	Lamp	No. of
Luminaire Length	Туре	Lamps
1x4	F32	2, 3
1x4	F28	2, 3
2x2	F14	2, 3, 4
2x2	F17	2, 3, 4
2x4	F32	2, 3, 4, 6
2x4	F28	2, 3, 4, 6
2x4	F44, F54	2, 3, 4

## **General Notes**

 Many luminaire components, such as reflectors, refractors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility.



# **K2A** Kleenseal KTR 200 recessed

# Cleanroom, T8, T8HO, T5, or T5HO

#### **Standards**


- · Certified to meet UL 1598 standards for wet location.
- · NSF is standard.

### Construction/Finish

- Recessed lightweight aluminum housing. Stainless steel housing is optional.
- Fits 1", 1-1/2", 2" and Tall 2" grid or flange mountings.
- 1/2" end conduit K.O.s for easy thru wiring.
- · Seismic support mounting is standard.

- One piece 20ga CRS door standard. Several other door options available.
- Door frame is secured to housing by captive stainless steel screws on 24" centers
- Door frame is retained to housing when opened for safety and ease during re-lamping.
- .125" prismatic acrylic lens is silicone sealed to door frame.
- · Closed cell polyethylene gasket seals door frame to grid tee or ceiling.
- · 200 psi hosedown.

### **Dimensions**





Some luminaires use fluorescent or high intensity discharge (HID) lamps that contain small amounts of mercury. Such lamps are labeled, "Contain Mercury" and/or the symbol "HG". Lamps that contain mercury must be disposed of in accordance with local requirements. Information regarding lamp recycling and disposal can be found at www.lamprecycle.org



© 2019 Signify Holding. All rights reserved. This document may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed All trademarks are owned by Signify Holding or their respective owners.