



Ordering Information

Catalog No.	Finishes	Track Mounting	Luminaire Compatibility
26075WH 26075BK	Matte White Matte Black	Compatible with ProSpec Track Systems. DO NOT USE with Monopoints.	Compatible with all Lytespan line and low voltage incandescent luminaires, 250W Max. Compatible with all Lytespan fluorescent and metal halide luminaires EXCEPT PowerWash, Lyteflood L39/L40, PowerArc Modular, SoffTech Metal Halide, Lytespot Metal Halide. DO NOT USE with Power Jack or ProSpec luminaires.

Description

Adapter module that mounts anywhere along the ProSpec track and accepts most Lytespan luminaires (see luminaire compatibility for exceptions).

Features

- Adapter Housing:** High-temperature impact resistant thermoplastic.
- Basic Lytespan Track Strip:** Die cast aluminum, with high-temperature impact resistant thermoplastic insulator, supporting electrical contacts. Accepts Lytespan luminaires.
- Track Attachment Fitting:** High-temperature impact resistant polycarbonate, rotates into track. Adapter module can be flipped 180° to access one or the other circuit.
- Clamping Knob:** Rotation of clamping knob secures steel clamping toggle to track.
- Attachment Lever:** Impact resistant polycarbonate. For mechanical/electrical connection to track.

Electrical

Unit is polarized and continuously grounded throughout. 250W load capacity.

Labels

cULus

Job Information

Type:

Job Name:

Cat. No.:

Lamp(s):

Notes:

Lightolier a Genlyte company

www.lightolier.com

631 Airport Road, Fall River, MA 02720 • (508) 679-8131 • Fax (508) 674-4710

We reserve the right to change details of design, materials and finish.

© 2005 Genlyte Group LLC • 0505