

Quebec BRP775

Mounting instruction

Instructions de montage

Montageanleitung

Montage instructie

Istruzioni di montaggio

Instrucciones de montaje

Instruções de montagem

Monteringsinstruktioner

Monteringsvejledning

Kokoonpano- ja kiinnitysohjeet

Montaj yönergesi

Οδηγίες συναρμολόγησης

Instrukcja montażu

Szerelési utasítások

Návod k montáži

Монтажная инструкция

					
					
Max. 7 Kg	0.10 m²	RG1			

BRP775

Neutral White	Warm White	LED	System Power (W)				
GRN53	GRN47	40	43.8	•	•	40°	-20°
GRN48	GRN42	36	39.4	•	•	40°	-20°
ECO65	ECO57	36	56.3	•	•	40°	-20°
ECO84	ECO73	36	78.7	•	•	40°	-20°
GRN40	GRN35	30	32.8	•	•	40°	-20°
ECO54	-	30	46.9	•	•	40°	-20°
ECO71	ECO61	30	65.6	•	•	40°	-20°
GRN33	GRN28	24	26.2	•	•	40°	-20°
ECO57	ECO50	24	52.4	•	•	40°	-20°
GRN24	GRN21	18	19.7	•	•	40°	-20°
ECO33	ECO29	18	28.1	•	•	40°	-20°
ECO43	ECO38	18	39.2	•	•	40°	-20°
GRN16	GRN14	12	13.1	•	•	40°	-20°
ECO22	ECO20	12	18.7	•	•	40°	-20°
ECO29	ECO25	12	26.2	•	•	40°	-20°

20028948_C





03/2015

Data subject to change


Printed in Spain

www.philips.com/lighting

PHILIPS



1a




1b




2a




2b




2c



2d




3




4a




4b








4c






5



OPEN & CLOSE BOWL





Tolerances:

All electrical and flux values are typical values at 25°C ambient.

	Flux	W
LED	+/- 7%	-
Vf LED	-	+7% / -12%
I-driver	+/- 5%	+/- 5%
	+/- 12%	+12% / -17%


Temperature protection:

Both LED and Driver have a temperature protection.

When for any reason the temperature of LED is too high the system first dims back to 50%, if it is still too hot it will switch off. If the driver is too warm it switches off. Power will return automatically when the temperature has dropped again.

T_c max. of Led module:

T_c max. = 80°C



Quebec BRP776

Mounting instruction

Instructions de montage

Montageanleitung

Montage instructie

Istruzioni di montaggio

Instrucciones de montaje

Instruções de montagem

Monteringsinstruktioner

Monteringsvejledning

Kokoonpano- ja kiinnitysohjeet

Montaj yönergesi

Οδηγίες συναρμολόγησης

Instrukcja montażu

Szerelési utasítások

Návod k montáži

Монтажная инструкция

					
					
Max. 6 Kg	0.094 m ²	RG1			

BRP776

Neutral White	Warm White	LED	System Power (W)				
GRN53	GRN47	40	43.8	•	•	40°	-20°
GRN48	GRN42	36	39.4	•	•	40°	-20°
ECO65	ECO57	36	56.3	•	•	40°	-20°
ECO84	ECO73	36	78.7	•	•	40°	-20°
GRN40	GRN35	30	32.8	•	•	40°	-20°
ECO54	-	30	46.9	•	•	40°	-20°
ECO71	ECO61	30	65.6	•	•	40°	-20°
GRN33	GRN28	24	26.2	•	•	40°	-20°
ECO57	ECO50	24	52.4	•	•	40°	-20°
GRN24	GRN21	18	19.7	•	•	40°	-20°
ECO33	ECO29	18	28.1	•	•	40°	-20°
ECO43	ECO38	18	39.2	•	•	40°	-20°
GRN16	GRN14	12	13.1	•	•	40°	-20°
ECO22	ECO20	12	18.7	•	•	40°	-20°
ECO29	ECO25	12	26.2	•	•	40°	-20°

20028636_B





03/2015

Data subject to change


Printed in Spain

www.philips.com/lighting


PHILIPS




1a




1b




2a




2b




2c




2d




3




4a




4b








4c






5



OPEN & CLOSE BOWL





Tolerances:

All electrical and flux values are typical values at 25°C ambient.

	Flux	W
LED	+/- 7%	-
Vf LED	-	+7% / -12%
I-driver	+/- 5%	+/- 5%
	+/- 12%	+12% / -17%

Temperature protection:

Both LED and Driver have a temperature protection.

When for any reason the temperature of LED is too high the system first dims back to 50%, if it is still too hot it will switch off. If the driver is too warm it switches off. Power will return automatically when the temperature has dropped again.

T_c max. of Led module:

T_c max. = 80°C

