

# PHILIPS

## Recessed spot light

59062 Smalu 125 RM 9W TW  
WH

white

LED



59062/31/I5



## versatile lighting for a smart home

Enjoy greater freedom with this intelligent Philips Smalu LED downlight. Comes in white aluminum with a frosted synthetic diffuser for even lighting. Can be remotely control within a click and dimmable with three color temperature options.

### Long lifespan

- Extremely long life 20,000 hours

### Advanced LED light

- Adjustable light intensity with dimmer switch
- Tunable 2700-6500K

### Energy saving

- Built-in LED, as part of the system
- 80% energy saving

### Premium quality

- Die-casted aluminum for a premium look and feel

# Highlights

## Extremely long life



A light source you can trust. Philips LED lights offer an extremely long-life of at least 20,000 hours (which equals 20 years on basis of an average use of 3 hours / day with an amount of at least of 13,000 on/off switching cycles). It feels so comfortable to think that you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

## Dimmable



Adjust the light intensity of the Philips LED lights with a dimmer switch (not included). This makes this light ideal for creating an ambience for any occasion, whether a cosy meal ? deux or chilling out with family and friends in your living room. Philips tested a number of wall dimmers that have proved to be compliant with our LED lights. A list of compatible dimmers is available in the downloads and support section.

## Tunable



This lamp is tunable. You can tune it to your preferred light color; from warm white (2700K) to cool daylight (6500K).

## Integrated LED light source



A light source you can trust. With integrated LED light source, you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

## 80% energy saving



Up to 80% energy saving compared to standard incandescent light sources.

## Premium materials



# Specifications

## Design and finishing

- Color: white
- Material: aluminium

## Extra feature/accessory incl.

- LED integrated: Yes

## Light characteristics

- Beam angle: 110 degree(s)
- Color rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Living- & Bedroom, Living- & Bedroom
- Style: Functional
- Type: Spot light
- EyeComfort: No

## Product dimensions & weight

- Cut out length: 12.5 cm
- Cut out width: 10.6 cm
- Height: 9.7 cm
- Length: 13.9 cm
- Net weight: 0.344 kg
- Recessed distance: 9.0 cm
- Width: 13.9 cm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 560
- Light color: 2700
- Mains power: 230 V
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Number of bulbs: 40
- Wattage bulb included: 0.25 W
- Maximum wattage replacement bulb: 0.3 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II – double insulated

## Packaging dimensions and weight

- EAN/UPC – product: 6947830428960
- Net weight: 0.344 kg
- Gross weight: 0.464 kg
- Height: 150.000 mm
- Length: 83.000 mm
- Width: 145.000 mm
- Material number (12NC): 915005189901



Issue date: 2023-11-08  
Version: 0.508

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)