


PHILIPS

Recessed spot light

59204 MESON GEN2 150
10W30KWH

white

LED



59204/31/H1



Essential lighting for a bright home

Illuminate your spaces with Philips Meson LED downlight, and enjoy soft, uniformly distributed light from a high quality diffuser and a LED light source. Installing this downlight fixture can be relatively easy and quick for homeowners.

Ease of use

- Space-saving design

Energy saving

- 80% energy saving

Highlights

Space-saving design
80% energy saving



Up to 80% energy saving compared to standard incandescent light sources.

Specifications

Design and finishing

- Color: white
- Material: synthetics

Extra feature/accessory incl.

- Diffused light effect: Yes
- LED integrated: Yes
- Photometric data available: Yes
- Centerpiece: Yes

Light characteristics

- Beam angle: 110 degree(s)
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Functional, Living- & Bedroom
- Style: Functional
- Type: Downlight
- EyeComfort: No

Product dimensions & weight

- Cut out length: 15 cm
- Cut out width: 15 cm
- Height: 16.7 cm
- Length: 16.5 cm
- Net weight: 0.135 kg
- Recessed distance: 4.7 cm
- Width: 16.5 cm

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 940 lm
- Bulb technology: LED, 230 V
- Light color: warm white
- Mains power: Range 220 V - 240 V, 50-60 Hz
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Number of bulbs: 45
- Wattage bulb included: 0.25 W
- Maximum wattage replacement bulb: 10 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II - double insulated

Design and finishing

- Color: white
- Especially designed for: Functional, Living- & Bedroom
- EAN/UPC - product: 6947830435913
- Beam angle: 110 degree(s)
- Net weight: 0.135 kg
- Cut out length: 15 cm
- Material: synthetics
- Style: Functional
- Gross weight: 0.191 kg
- Cut out width: 15 cm
- Color rendering index (CRI): 80
- Type: Downlight
- Height: 175.000 mm
- Height: 16.7 cm
- Lifetime up to: 15,000 hour(s)
- EyeComfort: No
- Length: 59.000 mm
- Width: 168.000 mm
- Material number (12NC): 915005501501
- Length: 16.5 cm
- Net weight: 0.135 kg
- Recessed distance: 4.7 cm
- Width: 16.5 cm
- Diffused light effect: Yes
- Total lumen output fixture: 940 lm
- Bulb technology: LED, 230 V
- Light color: warm white
- LED integrated: Yes
- Mains power: Range 220 V - 240 V, 50-60 Hz
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Number of bulbs: 45
- Wattage bulb included: 0.25 W
- Maximum wattage replacement bulb: 10 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II - double insulated
- Photometric data available: Yes
- Centerpiece: Yes



Issue date: 2022-06-12
Version: 0.451

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com