



PHILIPS
Recessed spot light
59260 ERIDANI 080 3W
40K WH
white
LED



59260/31/H3

Essential lighting for a bright home

The Philips Eridani LED Downlight is a flawless fit for a brilliant atmosphere. A soft, elegant cut in white evokes a simple touch for any home setting, accentuating intricate interiors of small corners and compact homes.

Match your interior style

- Available in various sizes

Light effect

- Even light distribution

Sustainable light solutions

- High quality LED light

Easy to Experience

- Long-lasting, high-powered LED technology

PHILIPS

Energy saving

- Instant, flicker-free start
- Built-in Philips conventional ballast
- Built-in LED, as part of the system
- 80% energy saving

Highlights

Available in various sizes
Even light distribution



High quality LED light



The LED technology, integrated into this Philips lamp, is a uniquely developed solution by Philips. While instantly turned on, it enables an optimal light output and brings out vivid colors in your home.

High-powered LED



Instant, flicker-free start

Instant, flicker-free start, with an electronic ballast

Energy efficient, long lasting
Integrated LED light source



A light source you can trust. With integrated LED light source, you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

80% energy saving



Up to 80% energy saving compared to standard incandescent light sources.

Specifications

Design and finishing

- Color: white
- Material: synthetics

Extra feature/accessory incl.

- Diffused light effect: Yes
- LED integrated: Yes
- Photometric data available: Yes

Miscellaneous

- Especially designed for: Functional, Living- & Bedroom
- Style: Functional
- Type: Recessed spot light
- EyeComfort: No

Product dimensions & weight

- Cut out length: 8.0 cm
- Cut out width: 8.0 cm
- Length: 9.2 cm
- Net weight: 0.046 kg
- Recessed distance: 4.2 cm
- Width: 9.2 cm

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 215 lm
- Mains power: Range 220 V - 240 V, 50-60 Hz
- Fixture dimmable: No
- LED: Yes
- Number of bulbs: 1
- Wattage bulb included: 3 W
- Maximum wattage replacement bulb: 3 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II - double insulated

Packaging dimensions & weight

- SAP EAN/UPC - Piece: 6947830437344
- EAN/UPC - Case: 6947830480555
- Height: 10.6 cm
- SAP Gross Weight EAN (Piece): 0.072 kg
- Weight: 0.072 kg
- Net Weight (Piece): 0.046 kg
- SAP Height (Piece): 106.000 mm
- SAP Length (Piece): 62.000 mm
- SAP Width (Piece): 102.000 mm
- Width: 6.2 cm
- Length: 10.2 cm



Issue date: 2019-04-01
Version: 0.283

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com