

PHILIPS

Recessed spot light

59521 MARCASITE 100 9W 30K
WH

white

LED



59521/31/H1



Essential lighting for a bright home

Philips Marcasite LED Downlight is a slim masterpiece for low height ceilings, giving elegance in soft light and perfect for accentuating ambiance in strategic locations at home. Take a minimalist feel to a new level with beautiful light.

Ease of use

- Space-saving design

Energy saving

- 80% energy saving

Highlights

Space-saving design 80% energy saving



Up to 80% energy saving compared to standard incandescent light sources.

Specifications

Design and finishing

- Color: white
- Material: plastic

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No
- Centerpiece: Yes

Light characteristics

- Beam angle: 110 degree(s)
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Functional
- Style: Functional
- Type: Downlight
- EyeComfort: Yes

Product dimensions & weight

- Cut out length: 10 cm
- Cut out width: 10 cm
- Height: 3 cm
- Length: 11 cm
- Net weight: 0.095 kg
- Recessed distance: 5 cm
- Width: 11 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 110 mm
- Total lumen output fixture: 600
- Bulb technology: LED, 240 V
- Light color: 3000
- Mains power: 220-240
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Number of bulbs: 40
- Wattage bulb included: 9
- Maximum wattage replacement bulb: 0.2 W
- IP code: IP20
- Class of protection: Class II

Design and finishing

- Color: white
- Especially designed for: Functional
- EAN/UPC - product: 6947830432653
- Warranty: 1 year(s)
- Beam angle: 110 degree(s)
- Net weight: 0.357 kg
- Cut out length: 10 cm
- Material: plastic
- Style: Functional
- Gross weight: 0.438 kg
- Cut out width: 10 cm
- Adjustable spot head: No
- Color rendering index (CRI): 80
- Type: Downlight
- Height: 117.000 mm
- Height: 3 cm
- Lifetime up to: 15,000 hour(s)
- EyeComfort: Yes
- Length: 36.000 mm
- Width: 114.000 mm
- Material number (12NC): 915005379401
- Length: 11 cm
- Net weight: 0.095 kg
- Recessed distance: 5 cm
- Width: 11 cm
- Diameter: 110 mm
- Dimmable with remote control: No
- Total lumen output fixture: 600
- Bulb technology: LED, 240 V
- Light color: 3000
- LED integrated: Yes
- Mains power: 220-240
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Number of bulbs: 40
- Wattage bulb included: 9
- Maximum wattage replacement bulb: 0.2 W
- IP code: IP20
- Class of protection: Class II
- Remote control included: No
- Centerpiece: Yes



Issue date: 2022-06-12
Version: 0.463

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com