

# PHILIPS

Recessed spot light

59774 POMERON 070 3W 27K  
SI

aluminium

LED



59774/48/H0



## Essential lighting for a bright home

Manipulate the direction of your light in different ways with Philips Pomeron LED spotlight's adjustable head in 2 axis rotation. With a stylish white design that enhances your décor, bask in strong, focused beam with an accented feel.

### Easy to Experience

- Adjustable light angle

### Energy saving

- Built-in Philips conventional ballast

# Highlights

Adjustable light angle

Energy efficient, long lasting

## Specifications

### Design and finishing

- Color: aluminium
- Material: metal

### Miscellaneous

- Especially designed for: Functional, Living- & Bedroom
- Style: Functional
- EyeComfort: No

### Product dimensions & weight

- Cut out length: 7.0 cm
- Cut out width: 7.0 cm
- Length: 9.0 cm
- Net weight: 0.082 kg
- Recessed distance: 6.2 cm
- Width: 9.0 cm

### Service

- Warranty: 1 year(s)

### Technical specifications

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 190 lm
- Mains power: Range 220 V – 240 V
- Fixture dimmable: No
- LED: Yes
- Number of bulbs: 1
- Wattage bulb included: 3 W
- Maximum wattage replacement bulb: 3 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II – double insulated



Issue date: 2023-11-08  
Version: 0.420

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)