


# PHILIPS

Recessed spot light


59776 POMERON 070 7W 27K  
WH

white

LED



59776/31/H0



## Essential lighting for a bright home

Manipulate the direction of your light in different ways with Philips Pomeron LED spotlight's adjustable head in 2 axis rotation. With a stylish white design that enhances your décor, bask in strong, focused beam with an accented feel.

### Easy to Experience

- Adjustable light angle

### Energy saving

- Built-in Philips conventional ballast

# Highlights

**Adjustable light angle**

**Energy efficient, long lasting**

# Specifications

## Design and finishing

- Color: white
- Material: metal

## Miscellaneous

- Especially designed for: Functional, Living- & Bedroom
- Style: Functional
- Type: Recessed spot light
- EyeComfort: Yes

## Product dimensions & weight

- Cut out length: 7.0 cm
- Cut out width: 7.0 cm
- Length: 9.0 cm
- Net weight: 0.120 kg
- Recessed distance: 7.1 cm
- Width: 9.0 cm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 390 lm
- Mains power: Range 220 V - 240 V
- Fixture dimmable: No
- LED: Yes
- Number of bulbs: 1
- Wattage bulb included: 1 W
- Maximum wattage replacement bulb: 7 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II - double insulated



Issue date: 2020-07-09  
Version: 0.427

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)