




PHILIPS

TrueLine


RC530B EL




					kg	kg
			A	B	VPC	PCV
Recessed	VPC	W8L150	1497	1450	4.3	
Recessed	PCV	W8L145		1450		4.4
Recessed Line	VPC/PCV	W8L145	1448		4.2	4.5



Optional: RC530Z EP SET WH



Inrush current





I _{max} (A)	19
T _{ref} (μs)	280

Condition:
Input voltage 220V


MCB	Luminaire's Max.
B-10A	15
B-13A	19
B-16A	24
B-20A	30
C-25A	37
C-10A	24
C-13A	32
C-16A	40
C-20A	49
C-25A	62



Recessed






Wieland







2

3





PCV
















4




5





Recessed Line





PoE

Condition Philips to specify to the customers (instruction):
 > to use UTP (Unshielded Twisted Pair) CAT5E or CAT6 cable.
 > the maximum length of the cable to be 20 meters.
 Apply a minimum radius of the Ethernet cable of 4x the cable diameter.

