Day-Brite by (s) ignify

Recessed

ClearAppeal 2x2

2CAX up to 4500 lumens



Day-Brite / CFI ClearAppeal LED recessed is a fully luminous aperture luminaire providing modern appeal to architectural spaces. Featuring a regressed aesthetic with balanced glare gradient, ClearAppeal delivers high performing even illumination and high visual comfort. Its architectural style, coupled with controls options, makes ClearAppeal an ideal choice for applications such as office, institutional, and healthcare, where energy savings and customized effect are desired.

Project: Location Cat.No Type: Lamps Qty Notes

installed between driver and sensor

SpaceWise only sensor, daylighting and occupancy, advanced grouping

Interact Pro RF sensor, enables wireless connected lighting control

Interact Office advanced wireless sensor bundle, integral SC1500 w/ IoT capabilities for enterprise scale

Interact Pro scalable sensor with integral daylight & occupancy sensing, advanced grouping with

GTD/SNSR^{4,6,7} UL924 listed Bodine GTD factory

dwell time

with dwell time

Antimicrobial Finish Wet location listed

SWZCS^{2,10}

SWZDT²

RADIO²

IAOSB^{2,10}

AG

ClearAppeal now offers AccuRender technology for the highest color quality at the highest efficacy.

Ordering guide - standard & wireless controls

Standard configurations available with all choices, unless otherwise noted. Base configurations selections indicated by blue.

example: 2CAXG38L840-2-DS-UNV-DIM-SWZCS

| Width | Family | Ceiling Type | (nominal delivered) | Efficacy | Color | | Length | 1 | nter fuser | Volt | age | Driver | | Options | |
|--|-----------------------------|-----------------|--|---------------------------------------|---|---|--------|-----|----------------------|--|--|---|--|--|---|
| 2 | CAX | G | | | | - | 2 - | DS | _ | | - | | - | | |
| 2 2' | CAX ClearAppeal Gen 2 | G Grid | Base configuration 38B 3800 Standard configurations 30L 3000 38L 3800 45L 4500 Other lumen packages may be ordered in increments of 100Im from 3000 to 4500 lumens | Blank Standard H ⁵ High | 835 840 850 <u>Accur</u> 930 935 | 80 CRI, 3000K 80 CRI, 3500K 80 CRI, 4000K 80 CRI, 5000K Render ⁸ 90 CRI, 3000K 90 CRI, 3500K 90 CRI, 4000K | 2 2' | 1 1 | Diffuse (smooth) | UNV 347 | Universal Voltage, 120-277 volt 347V | DIM ¹ SDIM LDE LDEH DALI | Dimming Step dimming to 40% input power Lutron LDE5, 5% dimming Lutron LDE1, 1% dimming DALI dimming | F1 F2 F1/D F2/5W F2/6W GLR BSL10LST ⁴ BSL6LST ⁴ DSC CHIC ³ ER100 ^{4,6,7} | 3/8" flex, 3 wire 18 gauge 6' 3/8" flex, 4 wire 18 gauge 6' 3/8" twin flex, 3 wire 18 gauge 6' for dimmable luminaires 3/8" single flex, 5 wire 18 gauge 6' for dimmable luminaires 3/8" single flex, 6 wire 18 gauge 6' for dimmable and emergency luminaires Fusing, fast blow Bodine 10W selftesting battery pack Bodine 6W selftesting battery pack Quick driver disconnect Chicago Plenum rated UL924 listed sensor bypass relay, factory installed between driver & |
| Ordering guide - PoE controls example: 2CAXG38L840-2-DS-LV-POE-IAO | | | | | | | | | GTD/E ^{4,6} | sensor UL924 listed Bodine GTD factory installed on driver input | | | | | |

example: 2CAXG38L840-2-DS-LV-POE-IAO

| Width | lth Family | | Ceiling Type | Lume (nomi | ns inal delivered) | Efficacy | | Color | | 1 | Center Diffuser |
|-------------|------------|--|-----------------|-----------------------------|--|----------------|--------------------------|--|-------------|---|----------------------------|
| 2 | CAX | | G | | | _ | | - | 2 – | | DS - |
| 2 2' | CAX Clea | rAppeal Gen 2 | G Grid | Standa 30L 38L 45L | ard configurations 3000 3800 4500 | Blank Standard | 830 835 840 850 | 80 CRI, 3000K 80 CRI, 3500K 80 CRI, 4000K 80 CRI, 5000K | 2 2' | | DS Diffuse (smooth) |
| Voltag | e | Driver POE - | | | Options | | | | | | |
| | | EMPOE 600lm integral emergency driver and battery pack IAO Integral Interact Office daylighting and occupancy sensor, enables wireless connected lighting control IAOSB Integral Office advanced wired sensor bundle integral SC2000 | | | | | | | | | |

w/IoT capabilities for enterprise scale projects

Accessories (order separately)

- FSF422 2'x2' surface mount field installation kit (field assembled)
- FMA22 2'x2' "F" mounting frame for NEMA "F" ceiling
- CAXGDS22L 2'x2' ClearAppeal Gen2 replacement lens • CAXGDS22LC - 2'x2' ClearAppeal Gen2 with controls replacement lens

SWZCS accessories (order separately)

• IRT9015 - handheld remote for grouping and configuration (at least one remote required for any SWZCS installation).

Footnotes

- 1 Integral controls options dimmable to 5% via wireless wall switch. Non-controls options are 0-10v dimmable to 1% for Standard configurations, and to 10% for Base configurations.
- Specify only with -DIM driver option.
- CHIC option not provided with air return functionality.
- Not available with 347V.
- High efficacy option may only be ordered with Standard lumen configurations.
- Must be installed in conjunction with a UL1008 device.
- Must be ordered with an integral sensing option.

ClearAppeal_LED_2x2_gen2 04/22 page 1 of 6

- AccuRender is 90CRI with R9>50.
- Option is qualified as Engineered-to-Order (ETO) ready. Lead times and minimum order quantities may vary, please consult factory.(DLC Standard efficacy only)
- 10 Must order IRT9015 Interact commissioning remote with each system order.











up to 4500 lumens

Application

- · Ideal for modern offices, institutional, retail, and healthcare applications.
- · Modern architectural styling to complementany space.
- Full width luminous lens provides smooth brightness and high visual comfort.
- Directs a controlled amount of light to higher angles to eliminate "cave effect" without creating glare.
- Available in standard efficacy and high efficacy (H) configurations up to 130lm/W.
- 80 CRI minimum source provides a balanced spectral power distribution.
- · AccuRender 90 CRI source provides preferred color quality.
- Suitable for use with NEMA G (15/16") and NFG (9/16") suspended t-grid ceilings. NEMA F flange ceilings require the FMA24 accessory (ordered separately).

Construction/Finish

- Robust and durable dieformed embossed steel housing and end caps.
- Molded one-piece acrylic diffuser may be removed without tools for access to LED boards and driver(s).
- Unique spring retainers ensure the diffuser is centered in the housing opening at all times.
- T-bar grid clips are built into luminaire end caps for quick and easy installation, no extra parts.
- Air return functionality is standard for all configurations. See air flow and noise data on page 4.

Energy data

| Configuration | Nominal CCT/ CRI | Flux (lm) | Input Power (W) | Efficacy (LPW) | DLC |
|---------------|---------------------|--------------|--------------------|-------------------|----------|
| 2CAXG38B835 | 3500K/80 | 3990 | 34 | 117 | Standard |
| 2CAXG38B840 | 4000K/80 | 4007 | 34 | 116 | Standard |
| 2CAXG30L835 | 3500K/80 | 3053 | 26 | 116 | Standard |
| 2CAXG30L840 | 4000K/80 | 3061 | 27 | 116 | Standard |
| 2CAXG30LH835 | 3500K/80 | 3023 | 24 | 124 | Standard |
| 2CAXG30LH840 | 4000K/80 | 3097 | 24 | 127 | Premium |
| 2CAXG38L835 | 3500K/80 | 3884 | 34 | 114 | Standard |
| 2CAXG38L840 | 4000K/80 | 3887 | 34 | 114 | Standard |
| 2CAXG38LH835 | 3500K/80 | 3797 | 30 | 126 | Premium |
| 2CAXG38LH840 | 4000K/80 | 3814 | 29 | 130 | Premium |
| 2CAXG45L835 | 3500K/80 | 4587 | 42 | 111 | Standard |
| 2CAXG45L840 | 4000K/80 | 4614 | 42 | 110 | Standard |
| 2CAXG45LH835 | 3500K/80 | 4612 | 36 | 127 | Premium |
| 2CAXG45LH840 | 4000K/80 | 4716 | 36 | 130 | Premium |

- Suitable for end to end continuous row mounting. 1" gap between luminaires requires chase nipple to accommodate through wiring (by others).
- Sheetmetal componets are multi-stage phosphate treated for maximum corrosion resistance and finish coat is high reflectance basked white enamel.
- Integral louvers on housing ends allow air from the heated space to return to a pressurized plenum.

Electrical

- $\boldsymbol{\cdot}$ Driver and LED board are accessible from below by easy removal of lens.
- Non-controls Base configurations 0-10V dimmable to 10%.
- · Non-controls Standard configurations 0-10V dimmable to 1%.
- Standard configurations with controls options dimmable via wireless switches (see below).
- Predicted L70 lumen maintenance up to 87,000 hours at 25°C ambient for all configurations.
- Emergency battery packs accessible from above. To estimate lumen output in emergency mode, multiply emergency pack wattage by luminaire efficacy, then by 1.10.
- The GTD/E option is used to bypass wall switches and allow luminaire operation on auxiliary power. Generator transfer requires installation in conjunction with a UL1008 listed device.
- The GTD/SNSR option is used to bypass integrated sensor control in the event of utility power loss. Generator transfer requires installation in conjunction with a UL1008 listed device.
- · Compliance to CAN ICES-005-A/ NEB-005-A and FCC Part 15-A.

Validation

- · cETLus listed for use in damp locations
- When ordered with -WL option code, suitable for use in wet locations with covered ceilings
- · Rated for direct contact with insulation (IC)
- · CCEA Chicago Plenum listed
- ClearAppeal luminaires are Designlights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers, www.designlights.org/QPL

Environment


• Rated for dry or damp locations in operating ambient temperatures 0-30°C (32-86°F). Many luminaire components, such as reflectors, refractors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility. Not suitable for natatorium environments.

Warranty

• 5 year manufacturer's limited warranty.

Visit signify.com/warranties for complete warranty information.

Dimensions



up to 4500 lumens

Wireless Controls Options

SpaceWise DT (SWZDT)

- Standalone daylight and occupancy sensing with advanced grouping, wireless mesh networking and dwell time.
- Commissioning via compatible Android phone and Philips Field App
- Dimming via compatible Zigbee wireless wall switch only (see link below for details)
- Register for the commissioning app at http:// registration.componentcloud.philips.com/ appregistration/
- · Integral sensing options may not be combined
- For more information including recommended switches, refer to the following: -

SWZDT - www.usa.lighting.philips.com/systems/lighting-systems/spacewise

Emergency Options (ER100)

- Power Sensing (Factory default) Recommended UL924 option requires unswitched power sense line, absence of voltage on the normal circuit triggers luminaire to 100% output
- Power Interruption Detection (Field option) Detects AC power interruption >30ms triggers 90 minute emergency mode with luminaire at 100% output

ClearAppeal shown with integral sensor



Interact Pro scalable sensor for Foundation, Advanced & Enterprise tiers (SWZCS and an evolution of SpaceWise)

- SWZCS is a connected sensor with integral occupancy and daylight sensing and supports wireless mesh connectivity.
- The sensor works in the Foundation mode (similar to SpaceWise) when configured without a gateway or in an Interact Pro Advanced or Enterprise mode if a compatible gateway is used.
- Interact Pro includes an App, a portal and a broad portfolio of wireless luminaires, lamps and retrofit kits all working on the same system.
- Startup is implemented via Interact Pro App (Android or iPhone) & BlueTooth connectivity.
 The App provides flexibility to choose between a gateway or non gateway mode for setup.
- Setup with the gateway requires wired internet access to the gateway. It is possible to add a gateway at a later point.
- Prepare project configuration steps remotely and use IRT9015 remote onsite to identify and group devices together.
- · Compatible with:
- SWS200 wireless scene switch
- Battery powered IP42 presence sensor OCC sensor IA CM WH 10/1
- Battery powered IP42 presence & daylight sensor OCC-DL sensor IA CM IP42 WH
- LCN3110: Battery powered IP65 presence sensor, OCC sensor IA CM IP65WH
- -LCN3120: Battery powered IP65 presence & daylight sensor, OCC-DL sensor IA CM IP65 WH
- For more information on Interact Pro visit: www.interact-lighting.com/ interactproscalablesystem

Radio only sensor (RADIO)

- Integral RADIO only sensor simply enables wireless mesh connectivity to the luminaire without any occupancy or daylight sensing.
- Ideal for applications where sensing functionality is managed by other Interact devices and the luminaire only needs to have wireless connectivity.

Interact Pro scalable sensor bundles for Enterprise tier

- IAOSB option in addition to occupancy and daylight sensing supports advanced IoT capabilities such as people estimation analysis, desk level temperature & humidity sensing, noise classification, and BLE beacon.
- Compatible with SWS200 wireless scene switch and Interact Ready wireless battery powered sensors.
- Use Interact software and insights to increase building efficiency, achieve building wide integration and optimize space through occupancy analytics.
- Requires compatible Gateway and internet connectivity for commissioning.
- For more information, visit:
 www.interact-lighting.com/office or
 www.usa.lighting.philips.com/systems/system areas/offices

Wired Controls Options Interact Office Wired (PoE)

- PoE based IoT connected lighting solution for large enterprises that span across multiple floors, buildings and require multiple gateways.
- Use Interact software and insights to increase building efficiency, achieve building wide integration and optimize space through occupancy analytics.
- IAOSB option in addition to occupancy and daylight sensing supports advanced IoT capabilities such as people estimation analysis, desk level temperature & humidity sensing, noise classification, and BLE beacon.
- PoE lighting controller is accessible from below.

- Integral sensor option for occupancy sensing (PIR) and/or daylight harvesting available for additional energy savings.
- Optional integral emergency controller and battery pack provides 600lm nominal output.
 Test switch and indicator light mounted on side of chassis on one end.
- Emergency battery has a 3 month pre-installed shelf life, and must be stored and installed in environments of 20C to 30C (-4F to 86F) ambient, and 45-85% relative humidity.
- For more information, visit: www.interactlighting.com/office or www.usa.lighting.philips. com/systems/system-areas/offices

Energy Data (PoE)

| Configuration | Nominal CCT/CRI | Flux (lm) | DC Power (W)* | Efficacy (LPW) |
|---------------|--------------------|-----------|---------------|----------------|
| 1CAXG30L840 | 4000K/80 | 3047 | 24 | 125 |
| 1CAXG38L840 | 4000K/80 | 3888 | 32 | 122 |
| 1CAXG45L840 | 4000K/80 | 4612 | 39 | 117 |

^{*}DC power supply


up to 4500 lumens

| | | Interact Pro scalabl | e system |
|---|------------|--|------------|
| | recent for | A CONTRACTOR OF THE PROPERTY O | |
| | Foundation | Advanced | Enterprise |
| Dimming, grouping, and zoning | ~ | ✓ | ~ |
| Bluetooth and ZigBee enabled | ~ | ✓ | ~ |
| Motion sensing and daylight harvesting | ~ | ✓ | ~ |
| Integration with 0-10V and phase dimming fixtures | ~ | ✓ | ~ |
| Code compliance | ~ | ✓ | ~ |
| Granular dimming and dwell time | ~ | ✓ | ~ |
| Energy reporting and monitoring | | ✓ | ~ |
| Scheduling | | ✓ | ~ |
| Demand response | | ✓ | ~ |
| BMS integration (BACnet) | | | ~ |
| Floor plan visualization | | | ~ |
| IoT sensors for wellness | | | ~ |
| IoT Apps for productivity | | | ~ |

Currently supported maximum system size

To be able to design the lighting system correctly for the customer, it is important to know the prime characteristics of the system, its possibilities and limitations.

| System level | | | | | | |
|--|---------------------|--|--|--|--|--|
| Total number of gateways | Unlimited | | | | | |
| Total number of devices | 200 per network | | | | | |
| luminaires with integrated sensors | 150 | | | | | |
| smart TLEDS | 150 | | | | | |
| Total number of ZGP devices (sensors and switches) | 50 | | | | | |
| · sensors | 30 | | | | | |
| · switches | 50 | | | | | |
| zones and groups | 64 | | | | | |
| Group level | | | | | | |
| Recommended number of lights | 40 (recommended 25) | | | | | |
| Number of ZGP devices | 5 | | | | | |
| Number of scenes | 16 | | | | | |




up to 4500 lumens

Air return



Integral louvers on housing ends allow air from the heated space to return to a pressurized plenum.

Return Air Data



| | | | 2x | 2 Return Air | - noise crite | ria | | |
|---------|-----|----|----|--------------|---------------|-----|------|----|
| CFM | 28 | 39 | 42 | 47 | 52 | 57 | 65.5 | 74 |
| NC (dB) | <15 | 26 | 31 | 33 | 38 | 42 | 44 | 46 |

Photometry

2x2 ClearAppeal recessed LED, base configuration, 3800 nominal delivered lumens

LER - 117

 Catalog No.
 2CAXG38B840-2-DS-UNV-DIM

 Test No.
 40558

 S/MH
 1.2

 Lamp Type
 LED

 Lumens
 4007

 Input Watts
 34

Comparative yearly lighting energy cost per 1000 lumens – \$2.05 based on 3000 hrs. and \$.08 pwr KWH.

The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.

Photometric values based on test performed in compliance with LM-79.

| Candle | power | | | |
|--------|-------|------|-------|---------|
| Angle | End | 45 | Cross | Back-45 |
| 0 | 1449 | 1449 | 1449 | 1449 |
| _ | | | | |

| 7.11.6.0 | | 1.0 | 4.055 | |
|----------|------|------|-------|------|
| 0 | 1449 | 1449 | 1449 | 1449 |
| 5 | 1432 | 1442 | 1448 | 1442 |
| 15 | 1368 | 1382 | 1393 | 1382 |
| 25 | 1245 | 1268 | 1281 | 1268 |
| 35 | 1077 | 1108 | 1124 | 1108 |
| 45 | 882 | 918 | 940 | 918 |
| 55 | 680 | 711 | 740 | 711 |
| 65 | 424 | 510 | 537 | 510 |
| 75 | 225 | 286 | 315 | 286 |
| 85 | 60 | 74 | 64 | 74 |

| light Distribution | | | | | | | | |
|--------------------|--------|-------------|--|--|--|--|--|--|
| Degrees | Lumens | % Luminaire | | | | | | |
| 0-30 | 1109 | 27.7 | | | | | | |
| 0-40 | 1801 | 44.9 | | | | | | |
| 0-60 | 3144 | 78.4 | | | | | | |
| 0-90 | 4008 | 100.0 | | | | | | |
| 0-180 | 4009 | 100.0 | | | | | | |

| Avera | Average Luminance | | | | | | | |
|-------|-------------------|------|-------|--|--|--|--|--|
| Zone | End | 45° | Cross | | | | | |
| 45 | 4096 | 4263 | 4368 | | | | | |
| 55 | 3895 | 4074 | 4237 | | | | | |
| 65 | 3298 | 3965 | 4176 | | | | | |
| 75 | 2850 | 3628 | 4000 | | | | | |
| 85 | 2273 | 2801 | 2401 | | | | | |

Coefficients of Utilization

| EFFECT | EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20) | | | | | | | | | |
|--------|--|-----|-----|-----|-----|-----|-----|-----|--|--|
| pfc = | 20 | | | | | | | | | |
| Ceil | | 80 | | | 70 | | 5 | 0 | | |
| Wall | 70 | 50 | 30 | 70 | 50 | 30 | 50 | 30 | | |
| RCR | | | | | | | | | | |
| 0 | 118 | 118 | 118 | 115 | 115 | 115 | 111 | 111 | | |
| 1 | 109 | 104 | 98 | 106 | 101 | 97 | 96 | 93 | | |
| 2 | 98 | 90 | 82 | 95 | 88 | 81 | 84 | 80 | | |
| 3 | 90 | 79 | 70 | 86 | 78 | 69 | 75 | 68 | | |
| 4 | 81 | 69 | 60 | 80 | 68 | 60 | 66 | 58 | | |
| 5 | 76 | 63 | 54 | 73 | 61 | 53 | 58 | 52 | | |
| 6 | 69 | 56 | 47 | 68 | 56 | 46 | 54 | 46 | | |
| 7 | 65 | 51 | 41 | 63 | 50 | 41 | 48 | 40 | | |
| 8 | 59 | 46 | 38 | 58 | 46 | 38 | 45 | 36 | | |
| 9 | 56 | 42 | 34 | 55 | 41 | 34 | 40 | 34 | | |
| 10 | 53 | 40 | 32 | 52 | 39 | 32 | 38 | 30 | | |

up to 4500 lumens

2x2 ClearAppeal recessed LED, standard configuration, 3800 nominal delivered lumens

LER - 114

 Catalog No.
 2CAXG38L840-2-DS-UNV-DIM

 Test No.
 40552

 Test No.
 40552

 S/MH
 1.2

 Lamp Type
 LED

 Lumens
 3888

 Input Watts
 34

Comparative yearly lighting energy cost per 1000 lumens – \$2.11 based on 3000 hrs. and \$.08 pwr KWH.

The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.

Photometric values based on test performed in compliance with LM-79.

Candlepower

| Angle | End | 45 | Cross | Back-45 |
|-------|------|------|-------|---------|
| 0 | 1412 | 1412 | 1412 | 1412 |
| 5 | 1395 | 1405 | 1411 | 1405 |
| 15 | 1334 | 1347 | 1357 | 1347 |
| 25 | 1214 | 1235 | 1247 | 1235 |
| 35 | 1050 | 1080 | 1095 | 1080 |
| 45 | 860 | 894 | 916 | 894 |
| 55 | 664 | 692 | 720 | 692 |
| 65 | 415 | 463 | 488 | 463 |
| 75 | 219 | 277 | 307 | 277 |
| 85 | 59 | 75 | 63 | 75 |

Light Distribution

| Degrees | Lumens | % Luminaire |
|---------|--------|-------------|
| 0-30 | 1081 | 27.8 |
| 0-40 | 1754 | 45.1 |
| 0-60 | 3063 | 78.8 |
| 0-90 | 3889 | 100.0 |
| 0-180 | 3889 | 100.0 |

Average Luminance

| Zone | End | 45° | Cross |
|------|------|------|-------|
| 45 | 3996 | 4152 | 4256 |
| 55 | 3804 | 3963 | 4126 |
| 65 | 3225 | 3596 | 3792 |
| 75 | 2778 | 3514 | 3896 |
| 85 | 2224 | 2816 | 2367 |

Coefficients of Utilization

| EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20) | | | | | | | | |
|--|-----|-----|-----|-----|-----|-----|-----|-----|
| pfc = | 20 | | | | | | | |
| Ceil | | 80 | | 70 | | | 50 | |
| Wall | 70 | 50 | 30 | 70 | 50 | 30 | 50 | 30 |
| RCR | | | | | | | | |
| 0 | 118 | 118 | 118 | 115 | 115 | 115 | 111 | 111 |
| 1 | 109 | 104 | 98 | 106 | 101 | 97 | 96 | 93 |
| 2 | 98 | 90 | 83 | 95 | 88 | 81 | 84 | 80 |
| 3 | 90 | 79 | 70 | 86 | 78 | 69 | 75 | 68 |
| 4 | 81 | 69 | 61 | 80 | 68 | 60 | 66 | 58 |
| 5 | 76 | 63 | 54 | 73 | 61 | 53 | 59 | 52 |
| 6 | 69 | 56 | 47 | 68 | 56 | 46 | 54 | 46 |
| 7 | 65 | 51 | 42 | 63 | 51 | 41 | 48 | 40 |
| 8 | 59 | 46 | 38 | 58 | 46 | 38 | 45 | 36 |
| 9 | 56 | 42 | 34 | 55 | 41 | 34 | 40 | 34 |
| 10 | 53 | 40 | 32 | 52 | 39 | 32 | 38 | 30 |

2x2 ClearAppeal recessed LED, high efficacy configuration, 3800 nominal delivered lumens

LER - 130

Catalog No. 2CAXG38LH840-2-DS-UNV-DIM

 Test No.
 40570

 S/MH
 1.2

 Lamp Type
 LED

 Lumens
 3815

 Input Watts
 29

Comparative yearly lighting energy cost per 1000 lumens – \$1.85 based on 3000 hrs. and \$.08 pwr

The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology

Photometric values based on test performed in compliance with LM-79.

Candlepower

| Angle | End | 45 | Cross | Back-45 |
|-------|------|------|-------|---------|
| 0 | 1393 | 1393 | 1393 | 1393 |
| 5 | 1377 | 1386 | 1392 | 1386 |
| 15 | 1316 | 1328 | 1337 | 1328 |
| 25 | 1197 | 1217 | 1228 | 1217 |
| 35 | 1035 | 1064 | 1078 | 1064 |
| 45 | 847 | 880 | 901 | 880 |
| 55 | 643 | 681 | 708 | 681 |
| 65 | 409 | 448 | 479 | 448 |
| 75 | 211 | 272 | 304 | 272 |
| 85 | 56 | 70 | 61 | 70 |

Light Distribution

| Degrees | Lumens | % Luminaire |
|---------|--------|-------------|
| 0-30 | 1065 | 27.9 |
| 0-40 | 1728 | 45.3 |
| 0-60 | 3012 | 78.9 |
| 0-90 | 3815 | 100.0 |
| 0-180 | 3815 | 100.0 |

Average Luminance

| Zone | End | 45° | Cross |
|------|------|------|-------|
| 45 | 3937 | 4090 | 4187 |
| 55 | 3682 | 3903 | 4058 |
| 65 | 3179 | 3480 | 3722 |
| 75 | 2672 | 3455 | 3855 |
| 85 | 2115 | 2639 | 2288 |

Coefficients of Utilization

| EFFEC | EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20) | | | | | | | | |
|-------|--|-----|-----|-----|-----|-----|-----|-----|--|
| pfc = | 20 | | | | | | | | |
| Ceil | | 80 | | | 70 | | | 50 | |
| Wall | 70 | 50 | 30 | 70 | 50 | 30 | 50 | 30 | |
| RCR | | | | | | | | | |
| 0 | 118 | 118 | 118 | 115 | 115 | 115 | 111 | 111 | |
| 1 | 109 | 104 | 98 | 106 | 102 | 97 | 96 | 93 | |
| 2 | 98 | 90 | 83 | 95 | 89 | 81 | 84 | 80 | |
| 3 | 90 | 79 | 70 | 88 | 78 | 69 | 75 | 68 | |
| 4 | 81 | 69 | 61 | 80 | 68 | 60 | 67 | 58 | |
| 5 | 76 | 63 | 54 | 73 | 61 | 53 | 59 | 52 | |
| 6 | 69 | 56 | 47 | 68 | 56 | 46 | 54 | 46 | |
| 7 | 65 | 51 | 42 | 63 | 51 | 41 | 48 | 41 | |
| 8 | 60 | 46 | 38 | 58 | 46 | 38 | 45 | 38 | |
| 9 | 56 | 42 | 34 | 55 | 42 | 34 | 40 | 34 | |
| 10 | 53 | 40 | 32 | 52 | 39 | 32 | 38 | 30 | |



© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify

Signify North America Corporation 400 Crossing Blvd, Suite 600 Bridgewater, NJ 08807 Telephone 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.