

Day-Brite

CFI

by @ignify

Recessed

EvoGrid

Architectural luminaire



Change within reach

Day-Brite / CFI EvoGrid LED recessed architectural luminaire combines style and affordability so that you can create comfortable, energy-efficient spaces within reach of your budget. The attractive 1x4, 2x2 and 2x4 configurations, as well as three color temperatures, complement any décor without distraction, thanks to a single lens enclosure and stylish, modern architectural aesthetics; yet they are priced similarly to specification grade fluorescent luminaires. EvoGrid makes it easy to transition into dimmable LED technology, with high energy efficiency that can reduce payback periods;

while the SpaceWise integrated wireless control option provides further energy savings that may qualify for additional rebate incentives. EvoGrid is also Interact ready, simplifying bringing the power of connected lighting to small and medium businesses.



interact
ready.

EV EvoGrid

Recessed architectural luminaire



Features

- Reliable performance up to 139 LPW
- Standard 0-10V dimming and optional integrated occupancy and daylight harvesting sensors
- Attractive single lens enclosure and modern architectural aesthetics
- Convenient luminaire access to LED boards from below
- Less than 2-7/8" deep housing requiring minimal plenum space
- Interact Pro compatible
- Optional air handling function
- EvoGrid luminaires are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers (<http://www.designlights.org/QPL>)
- cETLus listed for damp locations

Benefits

- LED luminaires that complement any décor within budget and without distraction
- Energy and cost-savings compared to dimmable fluorescent recessed luminaires
- Further enhance savings with (SpaceWise) integrated wireless control option
- Simple installation and negligible maintenance reduces labor and maximizes savings
- Upgradable as future requirements change

Luminaire	Catalog Number	Input Power	Efficacy
1x4	1EVG30L840	23.9	129.0
	1EVG38L840	29.5	128.1
	1EVG45L840	36.3	126.2
2x2	2EVG30L840	25.2	119.0
	2EVG38L840	33.3	115.6
	2EVG45L840	39.3	114.1
2x4	2EVG38L840	36.5	109.9
	2EVG43L840	40.6	107.8
	2EVG48L840	47.7	105.2
	2EVG54L840	54.8	102.7
	2EVG74L840	82.6	92.8
	2EVG38LH840	27.0	139.2
2x4 High Efficacy	2EVG43LH840	32.0	138.5
	2EVG48LH840	35.5	137.9
	2EVG54LH840	39.4	136.5
	2EVG74LH840	56.2	133.9

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

