


Landscape

94 Line

942 and 943 Emergency Step Lights

The Gardco 942/943 EMC luminaires combine the architectural styling and rugged weather-tight construction of the 94 Line product with a self-contained battery back-up system. This unique series provides a recessed indoor and outdoor emergency lighting alternative that meets NEC and Life Safety Code requirements. The horizontal 942EMC and vertical 943EMC aisle lights are recessed into wall surfaces, providing a clean, appearance. The indicator light is mounted behind the lens and the test switch is discretely placed within the cast faceplate horizontal ribs.



Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notes:	

example: 942EMCD/C26QFPG120BLPF

Ordering Guide

Prefix	Wall Type	Wattage	Faceplates	Voltage	Finish	Options
942 / 943 Integral Emergency - Cold Temp (EMC) 942 EMC Horizontal 943 EMC Vertical 943B25EMC 943 Mounted in 25" Bollard 943B40EMC 943 Mounted in 40" Bollard NOTE: Back housings for concrete pour applications (Types C) are available for pre-shipment. Contact factory for details.	D/C Drywall/Concrete Suitable for drywall and concrete pour applications. Also, if insulating material is present, it must be kept at least 3" away from luminaire. Type D/C units are thermally protected. NOTE: WALL TYPE applies to 942EMC and 943EMC only. Omit for 943B25 and 943B40 types.	942/943 Integral Emergency - Cold Temp (EMC) Only 26QF (1) 26w Quad Fluorescent lamp. One lamps operates in the normal mode and one lamp operates in the emergency mode.	Prismatic Glass 942EMC only DG Diffuse Glass RGD Ribbed Guard with Diffuse Glass LV Louver	120 277	BLPBlack PaintBRPBronze PaintWPWhite PaintNPNatural Aluminum PaintOCOptional Color Paint Specify RAL designation ex: OC-RAL7024.SCSpecify Mat Specify Must supply color chip.	F Fusing TP Tamper resistant screws


Timensions code into the appropriate box above. Omit WALL TYTPE for 943B25EM and 943B40EM. Note: Gardco reserves the right to refuse a configuration. Not all combinations and configurations are valid. Refer to notes below for exclusions and limitations. For questions or concerns, please consult the factory.

942EM/EMC


(127m

8"

22







†(216mm) † 943B40EM/EMC 943B25EM/EMC



Specifications

FACEPLATE

One-piece die cast aluminum, secured to housing with (2) recessed and captive tamperresistant hex head socket screws. Self-compensating single-piece silicone gasketing allows for varying wall textures.

LOUVER

Die cast louvers span the entire length of the faceplate, providing for vandal resistance and glare control.

DIFFUSE GLASS

The faceplate includes a 3/16" thick diffuse white opal flat tempered glass lens. The lens is internally sealed and mounted and provides a soft, uniform glow.

PRISMATIC GLASS

A 3/8" thick prismatic glass lens, internally sealed and mounted, refracts light forward and downward (942EM/EMC only.)

RIBBED GUARD

90° die cast louvers span the entire length of the faceplate over either a prismatic (942EM/ EMC only) or diffuse glass lens.

STEPLIGHT HOUSING

Corrosion resistant die cast aluminum construction.

BOLLARD

Extruded aluminum base with cast top section.

J-BOX

Die cast aluminum. Factory mounted to bottom of housing. Field-convertible to back mounting. Junction box includes three (3) threaded openings that accommodate 3/4" conduit.

ELECTRICAL

EMC Luminaires: In the event of power interruption, integral emergency battery pack will power (1) 26W compact fluorescent lamps at reduced light levels for a minimum of 90 minutes. Maintenance free battery is rated for ambient temperatures down to -4°F/-20°C. A momentary test switch and charging indicator light are standard. EMC units do not bear CUL label.

FINISH

Standard finishes are fade and abrasion resistant, electrostatically applied, thermally cured TGIC polyester powdercoat, applied after anodizing. Consult Factory for special colors.

LABELS

All luminaires bear UL Wet Location labels.

WARRANTY

5 year limited warranty. See signify.com/warranties for complete details and exclusions.

(s) ignify

© 2019 Signify Holding. All rights reserved. This document may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. All trademarks are owned by Signify Holding or their respective owners.

Signify North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Telephone 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone 800-668-9008