




Using Ledalite's revolutionary MesoOptics technology, PureFX offers the perfect blend of brightness, control and energy efficiency.

Ordering guide



Integrated Controls Please indicate with check mark. Upgrades & Accessories Please indicate with check mark. Response Daylight Single Zone (DS) Flex Whip (6' length) Drywall Kit





^{*} Nominal values within a range. Consult photometry data for CRI, color temp, lumens & distribution of chosen configuration. † Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

PureFX

1'x4', 4400 lm 3000/3500/4000K

Optical System

The optical frame assembly consists of an acrylic panel with a layer of protected MesoOptics film which efficiently provides a luminous, controlled, low glare 3-dimensional batwing distribution. The optical frame ends are constructed from die-formed cold-rolled steel assembled together with extruded aluminum profiles in a sturdy frame. The frame is hinged to allow easy access to the inside of the fixture. Maintenance can be performed from below the ceiling.

Housing

Die-formed, post-painted, 22 gauge cold-rolled steel housing. Multiple wire entrances are available (top or side) to allow continuous row mounting of fixtures. Optional frame restraint is available to provide additional safety support.

Mounting

Compatible with lay-in acoustical ceilings using an exposed 9/16", 15/16" or slot T-grid suspension system (NEMA types G, NFG & NFGS). Integral mounting tabs are provided which handle different T-grid heights.

Finish

Housing and Frame: Post-painted, high quality powder coat. Available in white only.

Weight

Maximum 25lb.

Electrical

LED boards are easily field replaceable. Fixtures are factory pre-wired and tested for all circuits. Driver access from below the ceiling. Optional armored cable flex whips are supplied in 6' lengths.

Standard Driver

Philips Advance Xitanium 0-10V, 1-100%. Class 2 rated output. Consult Philips Ledalite for other available drivers.

Standard Battery Pack

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = $10W \times luminaire$ efficacy x 1.1. Typical output: 900lm.

Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 is: **Reported** methodology is L_{70} (12k) >52,000 hrs.

Source Color

LEDs rated for standard color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 3 SDCM.

Controls

Available with integrated Response Daylight sensor, which dims the luminaire when daylight is present. Contact Philips Ledalite for additional functionality.

Approvals

Certified to UL, IES & CSA Standards. City of Chicago Approved CCEA (housing option C). Type IC Rated.

Warranty

Five-year luminaire limited warranty including LED boards and driver. www.philips.com/warranties.

Environment

Rated for dry or damp locations in operating ambient temperatures of 0-25°C (32-77°F). Many luminaire components, such as reflectors, refractors, lenses, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility. Damage caused by sulfur, chlorine, petroleum based solution or other contaminants are not covered under warranty. Not suitable for natatorium environments.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.

Options and Details

Mounting

T-Grid ceiling types

Works with 9/16" 3. 15/16"
flat T-Grid ceilings

Flat T-Grid ceilings.

For 9/16" slot T-grid ceilings.


For 9/16" slot T-grid ceilings.

fixture will sit 5/16"


Slot T-Grid

Integrates with most common


Ceiling types




Cross Section



Photometry @ CRI>80, 3500K



0% Up / 100% Down



Candela Distribution

/ertical		Hor	izontal A	ngle		Zonal
Angle	0	22.5	45	67.5	90	Lumens
0	1480	1480	1480	1480	1480	0
5	1485	1485	1488	1486	1490	142
15	1456	1473	1517	1559	1580	430
25	1371	1424	1526	1616	1653	699
35	1200	1273	1402	1490	1519	859
45	926	985	1095	1166	1188	831
55	638	679	754	814	828	666
65	379	409	462	500	505	452
75	164	199	236	259	256	238
85	31	51	57	58	56	63
90	0	0	0	0	0	0
95	0	0	0	0	0	0
105	0	0	0	0	0	0
115	0	0	0	0	0	0
125	0	0	0	0	0	0
135	0	0	0	0	0	0
145	0	0	0	0	0	0
155	0	0	0	0	0	0
165	0	0	0	0	0	0
175	0	0	0	0	0	0
180	0	0	0	0	0	0

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

RCR	Ceiling:		8	0			70			50		0
NCN	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		119	119	119	119	116	116	116	111	111	111	100
1		109	105	101	97	107	103	99	98	95	93	85
2		100	92	85	80	97	90	84	87	82	77	72
3		91	81	73	67	89	80	72	77	70	65	61
4		84	72	64	57	82	71	63	68	61	56	52
5		77	65	56	49	75	64	55	61	54	49	45
6		71	58	50	43	69	57	49	56	48	43	40
7		66	53	44	38	64	52	44	51	43	38	35
8		62	48	40	34	60	48	40	46	39	34	32
9		58	44	36	31	56	44	36	43	35	30	28
10		54	41	33	28	53	40	33	39	32	28	26

Avg. Luminance (cd/m2)

Vertical	H	orizontal Ang	gle
Angle	0	45	90
55	3832	4529	4974
65	3090	3766	4117
75	2183	3142	3408
85	1225	2253	2214

Distribution Summary

Hemisphere	0% Up / 100% Down		
Spacing Along (0°)	1.29		
Spacing Across (90°)	1.51		

PureFX

1'x4', 4400 lm 3000/3500/4000K

Optical Performance

Flux (lm)	4495	4381	4344
Efficacy (lm/W)	81.6	79.2	79.1
Power (W)	55.1	55.3	54.9
сст (к)	3985	3470	3071
CRI	83	83	83
R9	24	22	20
x	0.3837	0.4108	0.4356
у	0.3866	0.4017	0.4103
Duv	0.0040	0.0040	0.0030

Electrical Performance @ CRI>80, 3500K

Input Voltage	120V	347V	
Input Power	55.3W	47.2W	
Input Current	0.46A	0.14A	
Power Factor	0.994	0.980	
Total Harm. Distortion		7.0%	

Tested values – contact technical support for rated values. Off-state power zero unless certain controls are specified.



Tel. 800-668-9008