

PHILIPS

Recessed spot light

66022 3.5" 65K WHITE 7W

white

LED



66022/65/66



Essential lighting for a bright home

Never miss out the essentials with Philips Essmet LED downlight White. With long lasting LED light source and high quality anti glare diffuser encapsulated on a metal body, it is reliable and comfortable bright light without the hassle.

Match your interior style

- Available in various sizes

Light effect

- Even light distribution

Long lifespan

- Extremely long life 20,000 hours

Energy saving

- Built-in LED, as part of the system

Highlights

Available in various sizes Even light distribution



Extremely long life



A light source you can trust. Philips LED lights offer an extremely long-life of at least 20,000 hours (which equals 20 years on basis of an average use of 3 hours / day with an amount of at least of 13,000 on/off switching cycles). It feels so comfortable to think that you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

Integrated LED light source



A light source you can trust. With integrated LED light source, you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

Specifications

Design and finishing

- Color: white
- Material: metal

Extra feature/accessory incl.

- Adjustable spot head: No
- Diffused light effect: Yes
- Dimmable with remote control: No
- LED integrated: Yes
- Photometric data available: Yes
- Remote control included: No
- Centerpiece: No

Light characteristics

- Beam angle: 110 degree(s)
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Functional
- Style: Functional
- Type: Downlight
- EyeComfort: No

Product dimensions & weight

- Cut out length: 10.5 cm
- Cut out width: 10.5 cm
- Height: 6.8 cm
- Length: 12 cm
- Net weight: 0.05 kg
- Recessed distance: 1.2 cm
- Width: 12 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 120 mm
- Total lumen output fixture: 430
- Bulb technology: LED, 230 V
- Light color: 6500
- Mains power: 100–240 V
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Number of bulbs: 20
- Wattage bulb included: 7
- Maximum wattage replacement bulb: 6.5 W
- IP code: IP20
- Class of protection: Class I



Issue date: 2023-11-08
Version: 0.416

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com