



Ref. Certif. No.

SG-LE-01328

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

SYSTEME CEI D'ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE CERTIFICAT D'ESSAI OC

Product
Produit

Recessed luminaires
Office luminaires

Name and address of the applicant
Nom et adresse du demandeur

Philips Lighting Luminaires (Shanghai) Co., Ltd
2F, Building 6, No. 1805, Huyi Highway, Malu Town, Jiading District
201801 Shanghai, PEOPLE'S REPUBLIC OF CHINA

Name and address of the manufacturer
Nom et adresse du fabricant

NINGBO WEILINMA ELECTRONICS CO.,LTD., DONGQIAO
INDUSTRIAL ZONE, YINZHOU DISTRICT, 315161 NINGBO, PEOPLE'S
REPUBLIC OF CHINA

Name and address of the factory
Nom et adresse de l'usine

NINGBO WEILINMA ELECTRONICS CO.,LTD., DONGQIAO
INDUSTRIAL ZONE, YINZHOU DISTRICT, 315161 NINGBO, PEOPLE'S
REPUBLIC OF CHINA

Ratings and principal characteristics
Valeurs nominales et caractéristiques principales

Rated voltage: 220-240V~
Rated frequency: 50/60Hz
Rated power: See appendix
Protection Class: Class I
Degree of protection: IP20

Model/type Ref.
Ref. de type

RC099V LED26S/840 W60L60 GM, RC099V LED26S/865 W60L60 GM,
RC099V LED26S/840 W30L120 GM, RC099V LED26S/865 W30L120 GM
For all models refer to page 2

Additional information (if necessary)
Information complémentaire (si nécessaire)

Comply with IEC 62493(ed.1)

A sample of the product was tested and found
to be in conformity with
Un échantillon de ce produit a été essayé et a été
considéré conforme à la

IEC 60598-1(ed.8)
IEC 60598-2-2(ed.3)
IEC 62471(ed.1)

as shown in the Test Report Ref. No.
which forms part of this certificate
comme indiqué dans le Rapport d'essais numéro
de référence qui constitue une partie de ce
certificat

TÜV SÜD PSB Pte Ltd
083-1503933-000

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**

Date, 2015-08-03
CBS 15 07 75282 180


(Bingwen Zhang)



TÜV SÜD PSB Pte Ltd · 1 Science Park Drive · Singapore 118221

PSB Singapore

Model	Power	Lamp
RC099V LED26S/840 W60L60 GM	29W	12x(12x0,2W/LED module)
RC099V LED26S/865 W60L60 GM		
RC099V LED26S/840 W30L120 GM		6x(24x0,2W/LED module)
RC099V LED26S/865 W30L120 GM		
RC099V LED26S/840 W60L60 SUS GM		12x(12x0,2W/LED module)
RC099V LED26S/865 W60L60 SUS GM		
RC099V LED26S/840 W30L120 SUS GM		6x(24x0,2W/LED module)
RC099V LED26S/865 W30L120 SUS GM		
RC099V LED26S/840 W60L60 PCV GM		12x(12x0,2W/LED module)
RC099V LED26S/865 W60L60 PCV GM		
RC099V LED26S/840 W30L120 PCV GM		6x(24x0,2W/LED module)
RC099V LED26S/865 W30L120 PCV GM		
RC099V LED36S/840 W60L60 GM	34W	12x(11x0,25W/LED module)
RC099V LED36S/865 W60L60 GM		
RC099V LED36S/840 W30L120 GM		6x(22x0,25W/LED module)
RC099V LED36S/865 W30L120 GM		
RC099V LED36S/840 W60L60 SUS GM		12x(11x0,25W/LED module)
RC099V LED36S/865 W60L60 SUS GM		
RC099V LED36S/840 W30L120 SUS GM		6x(22x0,25W/LED module)
RC099V LED36S/865 W30L120 SUS GM		
RC099V LED36S/840 W60L60 PCV GM		12x(11x0,25W/LED module)
RC099V LED36S/865 W60L60 PCV GM		
RC099V LED36S/840 W30L120 PCV GM		6x(22x0,25W/LED module)
RC099V LED36S/865 W30L120 PCV GM		



Date, 2015-08-03
CBS 15 07 75282 180

Signature : (Bingwen Zhang)



PSB Singapore

TÜV SÜD PSB Pte Ltd • 1 Science Park Drive • Singapore 118221