

Track solutions

Philips Lightolier's CorePro LED Mini Cylinder is compatible with all LyteSpan track systems (Advent, Basic and Radius).



Advent

Circuits: 2, Shared Neutral
Lengths: 2ft, 4ft, 6ft, 8ft
Finishes: White, Black, Aluminum



Basic

Circuits: 1
Lengths: 2ft, 4ft, 6ft, 8ft, 12ft
Finishes: White, Black, Aluminum



Radius

Circuits: 1
Lengths: 2ft, 4ft, 6ft, 8ft
Finishes: White, Black, Aluminum



Actual Size



Features

- Efficacy: 107lm/w
- CCT: 2700 K & 3000 K
- CRI: 80, 90
- Lumens: 900lm
- Wattage: 9 W (max)
- Voltage: 120 V (50/60 Hz)
- CBCP: 3,554 (RNF)
- 50,000 hour rated life (L70)
- 5-year limited warranty*


Constructed of extruded aluminum and steel with a powder-coated finish.



* Visit philips.com/warranties for more on Philips Lightolier's 5-year limited warranty.

Track adapters

The product line offers a range of competitor adapters for retrofit and renovation projects to improve ROI by not replacing existing track installations and limiting down time during the install.



Available for: Capri (LTC08), Halo (LTH08) and Juno (LTJ08).
View LT08 spec sheet for more on CorePro LED mini Cylinder.



Track lighting

CorePro LED Mini Cylinder



Upgrade to LED with ease

Track heads that combine classic, small form design with the benefits of LED technology.

© 2017 Philips Lighting Holding B.V. All rights reserved.
Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

PLI-1430PM 05/17 philips.com/luminaires

Philips Lighting
North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Tel. 855-486-2216

Philips Lighting Canada Ltd.
281 Hillmount Rd,
Markham, ON, Canada L6C 2S3
Tel. 800-668-9008

CorePro LED Mini Cylinder

This mini cylinder delivers both lumen and CBCP performance equivalent to that of most 50W MR16 halogen luminaires while consuming 82% less energy and providing easy maintenance.

The completely integrated driver, thermal management and unitized optics provide sleek aesthetics while delivering a uniform beam, making it the easy choice for many retail, residential, and hospitality accent lighting needs.



Benefits

- No need to replace halogen lamps and bi-pin sockets.
- No compatibility concerns with electronic transformers.
- Provides the efficiency, output and lifetime only an integrated LED solution can offer.
- Consumes 82% less energy than a 50W MR16.
- Higher flux than available LED MR16 lamps.*
- Hot targeted within a 3-step Macadam Ellipse
- CrispWhite enhancement for perfect combination of warm colors and white that stands out (90 CRI/ 3000K only).

* Based on data available at time of product launch.



Actual Size

CrispWhite technology

90 CRI/ 3000K only

The Lumileds 90 CRI/ 3000K CrispWhite technology combines the warm, saturated colors of high CRI with crisp and vibrant whites. The small form factor and high quality of the light make this an impactful option for retail display areas.

Learn more at: www.philipslumileds.com/products/luxeon-cob-with-crispwhite




CorePro LED
Mini Cylinder

Designed with simplicity in mind

An affordable solution to convert from traditional technologies to an integrated LED fixture that houses the driver, LED and optics in one compact design.

Available beam patterns include 23° narrow and 35° wide floods. Additional design features includes ELV dimming and compatible track adapters.



Ordering guide

Series	Track Adapter	Lumens	Beam Spread	CRI/CCT	Finish	Options	Version
LT		08					VA
LT CorePro LED Mini Cylinder	– Lightolier C Capri ¹ H Halo J Juno	08 900lm	RNF Narrow Flood (23°) RWF Wide Flood (35°)	827 80CRI/2700K 830 80CRI/3000K 927 90CRI/2700K 930 90CRI/3000K ²	AL Alum. ¹ BK Black WH White Finishes above	— None (leave blank) CW CrispWhite ²	VA Ver. A VA Ver. A

1. The Capri (C) track adapter is not available with the Aluminum (AL) finish option.
2. The CrispWhite (CW) option is available for the 90 CRI/ 3000K (930) CRI/ CCT configuration only.
For other configurations and variations please contact the factory.factory