

Project: _____


Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____



Ordering Guide

Example: P9600 12 A

Product Code	P9600	
Pole Height	12	12'
	14	14'
	16	16'
Finish	A	Black
	B	White
	G	Verde
	H	Bronze
	J	Green

Specifications

HOUSING:

356-T6 Sand Cast Aluminum. 6063-T6 Extruded aluminum . Anchor rods are hot dipped galvanized steel . Tenon is 356 HM sand cast aluminum.

FINISH:

A durable polyurethane enamel finish is applied after assemblies are shot blasted to create a surface profile which allows for the highest level of paint adhesion. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B-117-64 and ANSI/ASTM G53-77 specifications. For larger projects where a custom color is required, contact the factory for more information.

WARRANTY:

Three-year limited warranty.

P9600 P9600

Pole

Specifications

Tenon/Top:

3" OD

Bolt Circle:

9" - 10"

Anchor Rods:

(4) 3/4" dia. x 19"

Base Dimensions:

10 1/4" sq.

Hand Hole :

2" x 4" Oval

Shaft:

6" to 4" Tapered Fluted

Wall Thickness:

0.125 Aluminum

Height :

12', 14', 16'

Pole EPA Values

Windspeed(mph)	Height		
	12'	14'	16'
80	26.9300	18.2200	15.5200
100	16.9900	11.4400	9.6600

