



X-tend LED troffer


RC115B

Mounting instruction


V1.0




Product Type	Size (mm)	Power	Voltage	Frequency	CCT	lumen output	
RC115B LED35S/840 PSU W60L60	595x595x41	38W	220-240V~	50/60Hz	4000K	3500lm	2.8
RC115B LED35S/840 PSD W60L60	595x595x41						2.8
RC115B LED35S/840 PSU W30L120	295x1195x41	36W					2.7
RC115B LED35S/840 PSD W30L120	295x1195x41						2.7
RC115B LED35S/840 PSU W60L120	595x1195x41	34W					4.7
RC115B LED35S/840 PSD W60L120	595x1195x41						4.7
RC115B LED35S/840 PSU W60L60 S	595x595x41	38W					2.8
RC115B LED35S/840 PSU W30L120 S	295x1195x41						2.7
RC115B LED35S/840 PSU W60L120 S	595x1195x41						4.7





RC115B LED35S/840 PSU W60L60
RC115B LED35S/840 PSD W60L60
RC115B LED35S/840 PSU W60L60 S



RC115B LED35S/840 PSU W30L120
RC115B LED35S/840 PSD W30L120
RC115B LED35S/840 PSU W30L120 S



RC115B LED35S/840 PSU W60L120
RC115B LED35S/840 PSD W60L120
RC115B LED35S/840 PSU W60L120 S




X-tend LED troffer

RCI15B

Mounting instruction

V1.0

A Recessed




Adjust the luminaire position to fit ceiling well

DANGER – RISK OF FIRE

- Shall not be installed in residential premises

SCI= 50mm MIC= 50mm SCB=50mm HCB= 100mm

Safety chain



The product should install safety chain (Safety chain is not included in package).



Please read this manual carefully before using the product.



1. For indoor use only.
2. The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
3. The luminaire shall under no circumstances be covered or abutted with building insulation or be installed in a residential installation.
4. The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.
5. The luminaire is complied to IEC 60598 and AS/NZS 60598.
6. Safety chain is necessary.