

Project: _____


Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____



Ordering Guide

Example: 551S-4 thru 564S-4 ABS

Product Code	551S-4 thru 564S-4	Post Top Bracket Arms
Finish	ABS	Antique Brass
	ACP	Antique Copper
	ARD	Antique Red
	ASI	Antique Silver
	BLK	Black
	BRN	Brown
	BRZ	Bronze
	FGN	Forest Green
	GRA	Granite
	IRN	Ironstone
	RBZ	Rustic Bronze
	SRT	Shadow Rust
	VBZ	Verde Bronze
	VCP	Verde Copper
	VGN	Verde
	VTC	Vintage Copper
	WBZ	Weathered Bronze
	WHT	White

Specifications

CONSTRUCTION:

Cast aluminum bracket arms with decorative scrolls, cast aluminum bottom knobs, cast aluminum center hub with removable cast aluminum cap, welded construction. When center mount is specified, 1 piece of 3" dia. x .125" Wall at 12" long aluminum tubing supplied instead of top cap. Tubing protrudes out of center hub 8".

FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

MOUNTING:

Bracket arms fit over 4" dia. post. See specification sheet for other bracket options.

