

# CHLORIDE

by 

## Exit/Emergency

R series

Remote lighting fixture



Project: \_\_\_\_\_  
Location: \_\_\_\_\_  
Cat.No: \_\_\_\_\_  
Type: \_\_\_\_\_  
Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
Notes: \_\_\_\_\_

### Example: RW120P13

R			
<b>Series</b>	<b>Mounting Configuration</b>	<b>Battery</b>	<b>Lamp Wattage</b>
R - R-Series	W - Wall P - Pendant C - Ceiling	Incandescent <b>Blank</b> - 120 V  Compact Fluorescent <b>120</b> - 120 VAC <b>277</b> - 277 VAC	AC Only <b>HF</b> - 150 W A19 Incandescent <sup>1</sup> <b>P13</b> - 13 W Compact Fluorescent <b>P26</b> - (2) 13 W Compact Fluorescent  Emergency Only, Incandescent <sup>3</sup> <b>HF7</b> - 6 V, 7 W Halogen <b>HF10</b> - 6 V, 10 W Halogen <b>HF12</b> - 6 V, 12 W Halogen <b>THF12</b> - 12 V, 12 W Halogen  AC/Emergency Operation <b>HFP7</b> - 7 W Compact Fluorescent <sup>2</sup>

### Accessories (Order Separately)

**AR** - 25° Angled Dome Reflector  
**OB3** - 3-Way Explosion Proof 3/4" Conduit Hub  
**SEA** - Swivel Elbow Arm for Use With Pendant Mount Fixture to Connect to OB3 or IX Unit  
**SDR** - Straight Dome Reflector

### Footnotes

- <sup>1</sup> Lamps not provided.  
<sup>2</sup> For normally on use exclusively with IXP14 emergency power unit. The maximum remote mounting distance from the IXP14 is 8 feet.  
<sup>3</sup> Lamp provided.

### codes and standards

- UL 924 and 844 listed
- Suitable for wet locations
- NFPA 70 and NFPA 101, NEC, IBC, BOCA, and OSHA illumination standard
- Suitable for use in Class I, Div. 1 & 2, Groups C & D; Class I, Zone 1 & 2, Groups IIB & IIA; Class II, Div. 1 & 2, Groups E, F & G; Class III, Div. 1 & 2 hazardous location areas
- NEMA 3, 4, 4X
- Temperature performance rating T6 (maximum ambient temperature 160°C)

### construction

- Copper free cast aluminum enclosure designed to withstand the pressure of explosions generated by internal arc without propagating them into the hazardous atmosphere.
- Enclosure has a corrosion resistant, epoxy powder coat finish.
- Includes high impact, heat resistant globe with a cast aluminum globe guard, and stainless steel hardware.
- Ceiling and wall mount fixtures have universal junction box with four tapped holes for 3/4" rigid conduit (3 close-up plugs provided).
- Pendant mount fixture has 3/4" top hub.

### electronics

- Compatible with medium base incandescent or 13 W compact fluorescent lamps for non-emergency application.
- Available with low voltage halogen lamps and 7 W fluorescent lamps when powered by IX Series emergency lighting unit.

### lamps

- Illumination is accomplished with halogen incandescent or compact fluorescent lamps protected with a heat-resistant globe.

### warranty

- Five full years on electronics and unit (excluding lamps).



# R Remote lighting fixture

120/277VAC

## dimensions

