

by (Signify

Landscape

94 Line

940 Recessed Bricklights

The Gardco 940 brick lights are architecturally styled luminaires of minimal scale precisely constructed of die cast aluminum. The 940 was specifically designed to incorporate long-life compact fluorescent lamps and to be used in all types of wall construction. A field-convertible junction box further enhances its design flexibility. Self-compensating silicone gasketing excludes moisture, insects and contaminants, regardless of the wall surface texture. A choice of three (3) architecturally designed faceplates allows for a variety of applications.

0	•
9	•
Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notes:	

Ordering Guide example: 940UUTypeLV120BLP

Prefix 940	Wall Type	Wattage	Faceplates	Voltage	Finish
940 NOTE: Back housings for concrete pour applications (types U and C) are available for pre-shipment. Contact factory for details.	U Universal Suitable for all wall types including drywall, direct burial in insulation and concrete pour. C Concrete Pour Suitable for concrete pour applications only.	U Type 7/9TF 120V only 13TRF 18TRF C Type INC 60w maximum, 120V only	LV Louver PG Prismatic Glass DG Diffuse Glass	120 277 347	BLP Black Paint BRP Bronze Paint WP White Paint NP Natural Aluminum Paint OC Optional Color Paint Specify RAL designation ex: OC-RAL7024. SC Special Color Paint Specify. Must supply color chip.

Enter the order code into the appropriate box above. Note: Gardco reserves the right to refuse a configuration. Not all combinations and configurations are valid. Refer to notes below for exclusions and limitations. For questions or concerns, please consult the factory.

TF - Twin Tube Compact Fluorescent TRF - Trpile Tube Compact Fluorescent INC - Incandescent

94 Line 940 Recessed Bricklights

Specifications

GENERAL

The Gardco 940 brick lights are architecturally styled luminaires of minimal scale precisely constructed of die cast aluminum. The 940 was specifically designed to incorporate long-life compact fluorescent lamps and to be used in all types of wall construction. A field-convertible junction box further enhances its design flexibility. Selfcompensating silicone gasketing excludes moisture, insects and contaminants, regardless off the wall surface texture. A choice of three (3) architecturally designed faceplates allows for a variety of applications.

FACEPLATE

All faceplates are constructed of one-piece die cast aluminum and are secured to the housing with two (2) recessed and captive hex head socket screws.

Self-compensating single-piece silicone gasketing completely seals the luminaire and allows for varying wall thicknesses.

LOUVER

Die cast louvers span the entire length of the faceplate, providing for vandal resistance and glare control.

DIFFUSE GLASS

The faceplate includes a 3/16" (.48 cm) thick diffuse white opal flat tempered glass lens. The lens is internally sealed and mounted and provides a soft, uniform glow.

PRISMATIC GLASS

A 1/4" (.64cm) thick prismatic glass lens, internally sealed and mounted, refracts light forward and downward.

HOUSING

The housing is corrosionresistant die cast aluminum.

J-BOX

The field convertible junction box is die cast aluminum. It is shipped factory-mounted to the back of housing. The box can be easily positioned on the bottom of the luminaire via two (2) phillips head screws. Each J-box includes three (3) threaded openings (one on each side and one on the bottom) that accommodate 3/4" (1.91 cm) conduit.

ELECTRICAL:

FLUORESCENT UNITS: High power factor ballast is provided standard. 940 luminaires accept 7/9W twin or 13W or 18W triple tube compact fluorescent lamps.

INCANDESCENT UNITS:

Luminaires are provided with a medium base socket with a nickel plated screw shell. Each accepts up to a 60W T-10 lamp.

FINISH

Each standard color luminaire receives a fade and abrasion resistant, electrostatically applied, thermally cured, triglycidal isocyanurate (TGIC) textured polyester powdercoat finish. Standard colors include bronze (BRP), black (BLP), white (WP), and natural aluminum (NP). Consult factory for specifications on optional and custom colors.

LABELS

All luminaires bear UL or CUL (where applicable) Wet Location labels.

WARRANTY

5 year limited warranty. See signify.com/warranties for complete details and exclusions.

Dimensions







