

**PHILIPS
LIGHTOLIER**

Downlighting

LyteCaster Lytening



Increase the **beauty** and **value** of your home

Philips Lightolier LyteCaster Lytening IC/Non-IC frame-in kits are designed for convenience. Our remodelers are dual-rated for both insulated and non-insulated ceilings, so there is no guess work involved.

One of the most overlooked aspects of a remodel is the lighting. Done well, it will enhance the beauty of the space, increase the value of the home, and provide a more useful and productive environment. The task is to achieve that look without looking like you remodeled. Lytening, a leader in residential lighting, offers a recessed downlight for existing ceilings that is easy to install and provides an exceptional finished look.




LyteCaster Lytensing frame-in kits

A unique mounting design provides pressure above the ceiling, up to 2" thick, while three unobtrusive feet, 20/1000th of an inch thick, hold from below the ceiling. The result, a superior finished look that holds tight against the ceiling eliminating sagging and light leaks while providing a clean, finished look.

Unitized optic system ensures consistent lamp alignment and performance.

AirSeal ready – complies with WSEC and MEC codes with proper gasketing.
(LAS56R sold separately)

Three small flange points, only 20/1000th of an inch thick, make a clean, flush trim appearance at the ceiling.



5" Frames
Catalog Number
1004ICR
1004SICR

Open Downlight Trims					Eyeball	Enclosed Diffuser	Wall Washer
Specular Reflector	Specular Cone	Satin Cone	Baffles	White Splay			
1045	1012	1008	1005	1071	1022	1021	1085
1046	1013	1010	1005WH		1022WH	1024	
1046CD	1013CD		1076		1082	1090	
	1013BK		1076WH		1088		
	1013WH				1088GW	1177LX, 1178LX	
					1088WH		

6 3/4" Frames
Catalog Number
1104ICR
1104SICR

Open Downlight Trims								
Specular Reflector	Specular Cone	Satin Cone	Baffles	Cross Blades	White Splay	Eyeball	Enclosed Diffuser	Wall Washer
1143	1112	1108	B17	1132	B16	1182	1178LX	1185
1144	1113	1110	B17WH		1170M1		1177LX	
1144CD	1113CD		1105		1171		1121, 1124	
	1113BK		1105WH				1126, 1128	
	1113WH		1176				1190	
			1176WH				1177SH, 1178SH	

Deep housing

Shallow housing



Visit philips.com/warranties for more information on the standard 5-year limited warranty.



© 2016 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting North America Corporation
200 Franklin Square Drive, Somerset, NJ 08873
Tel. 855-486-2216

Philips Lighting Canada Ltd.
281 Hillmount Rd, Markham, ON, Canada L6C 2S3
Tel. 800-668-9008