

PHILIPS
LIGHTOLIER

Downlighting

LyteCaster Accent



**Design
versatility**
to fit any space

Simple, Reliable and **Designed** to Last

The Philips Lightolier LyteCaster 3" LED Accent is a versatile family designed for commercial and residential areas in both new construction and remodel applications. The LED product family is designed for peak performance, extended lifetime and reduced energy loads. LyteCaster's shallow luminaire height and 3 part modular system provides for easy installation and upgradeability in any space.



Pinhole
trim shown



Style, Variation and Modularity

A single light engine can be specified in a round or square style to allow you to customize your lighting solution to best suit the application. Reflector finishes include chrome, diffused and white and flange finishes are available in white or aluminum. Accessory films and replaceable optics also available.

Unmatched Performance

The integrated LED family is an affordable solution to traditional low-voltage luminaires with MR16 lamps. With efficacies ranging up to 80 lm/W, LyteCaster LED Accent offers visual comfort with no visible striations in a wide range of beam spreads, color temperatures and CRIs to choose from. Configurations are Title 24 compliant and Energy Star certified.

Model	Beam	CBCP (cd)	Power	Flux (lm)	Efficacy (lm/W)	Life (hr)	Chromaticity
LyteCaster LED Accent*	22°	3690	11W	819	69.4	50,000	3-step
LytePoint with LED MR16**	24°	2840	15W	650	54.2	30,000	6-step
LytePoint with LV Halogen MR16***	24°	2500	57W	800	14.0	6,000	n/a

Data values are based on total system outputs and not standalone light sources.

* L308830NF ** 10MR16/F24 3000 DIM HO 10/1 *** 50MR16/MFL24 EXZ

Round: White (finish shown)



Square: Aluminum (finish shown)






Shallow

Construction Design

The 3 1/2" shallow luminaire height saves plenum space without compromising the 60 ° physical and reflected cutoff.



Complete product = Frame-in kit + Light engine + Trim Order each separately

Ordering guide: Frame-In kit

Series	Frame type	Dimming	Input voltage
L3	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
L3 LyteCaster 3" Accent	A AirSeal IC, New Construction, Screw	E ELV/Triac dimming	1 120V
	AN AirSeal IC, New Construction, Nail		
	C Remodeler Non-IC	Z10 0-10V	U Universal (120/277V)
	N New Construction Non-IC		

Ordering guide: Light engine

Series	Lumens	CRI	CCT	Beam	Option
L3	08	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
L3 LyteCaster 3" Accent	08 800	8 80	27 2700K	S Spot, 17°	CW CrispWhite ¹
			30 3000K	NF Narrow flood, 22°	
			35 3500K	F Flood, 33°	
		9 90	27 2700K	S Spot, 17°	
			30 3000K	NF Narrow flood, 22°	
				F Flood, 33°	

Note: Nominal beam degrees provided. See spec sheets for exact ° for individual luminaire types.

Ordering guide: Trim

Series	Shape	Luminaire type	Finish	Flange
L3	R	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
L3 LyteCaster 3" Accent	R Round	D Downlight	C Chrome cone	blank White flange
		A Adjustable	D Diffuse cone	
		LW Lensed wall wash	W White cone	blank White flange
		B Baffle downlight	W White baffle	
		AB Adjustable baffle		
	S Square	G Gimbal	W White	blank White flange
			B Black	
			A Aluminum	blank White flange
		AP Adjustable pinhole	W White	
			A Aluminum	
	S Square	D Downlight	D Diffuse cone	blank White flange
		A Adjustable	W White cone ²	
	S Square	LW Lensed wall wash		blank White flange
	R Round	S Shower light		W White flange
	S Square			A Aluminum

Accessories: Films & holders, and field replacement optics are also available to achieve desired lighting effects. See spec sheets for further details.

1. 90 CRI/3000K is only available with the CrispWhite option.

2. White cone only available with white flange

Note: For 4000K, consult factory



©2015 Koninklijke Philips N.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

PLI-1502BN 04/15 philips.com/luminaires

Philips Lighting
North America Corporation
200 Franklin Square Drive
Somerset, NJ 08873
Tel. 855-486-2216

Imported by: Philips Lighting,
A division of Philips Electronics Ltd.
281 Hillmount Rd.
Markham, ON, Canada L6C 2S3
Tel. 800-668-9008