






| Project: | |
|-------------|--------------|
| Spec Type: | |
| Catalog No: | 4122SxxxL9BE |
| Qty | |
| Line Notes: | |

Specifically designed to blend high performance LED technology with versatile options to suit any area, VersaForm allows you to enjoy the latest LED energy efficiencies in concert with your unique style, and as your needs evolve, it's simple to change or upgrade with our unique detachable light engine.

Ordering guide



^{*} Nominal values within a range. Consult photometry data for color temp, lumens & distribution of chosen configuration.

Upgrades & Accessories Please indicate with check mark.



[†] Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

VersaForm

2'x2', 3000 lm CRI 90 3500K

Optical System

The optical frame assembly consists of integrated LED arrays edge lighting a light guide panel in order to deliver uniform controlled light through a lower lens. The optical frame ends are constructed from die-formed cold-rolled steel, assembled together with extruded aluminum profiles in a sturdy frame. The frame is hinged (side marked) to allow easy access to the inside of the fixture. Maintenance can be performed from below the ceiling.

Finish

Housing and frame painted, high quality, powder coated matte white only.

Housing

Die-formed, post painted, 22 gauge cold-rolled steel. Wire entrance with additional knock-out available on top side for electrical connections.

Weight

Maximum 28lbs (2x4); 21lbs (1x4); 15lbs (2x2).

Electrical

Factory pre-wired with driver safety disconnect.

Mounting

Recessed: Fixtures can be fastened directly to the T-bar grid and/or tied-off to the building structure. Optional drywall kit trim mount can be fastened to a wood frame or with hangar wire. Continous row mounting not available with drywall kit trim mounts.

Surface: Fixtures can be mounted over recessed junction box and side entry also available.

Standard Driver

Philips Advance Xitanium 0-10V, 1-100%, Class 2 rated output. Consult Philips Ledalite for other available drivers.

Standard Battery Pack

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = $10W \times luminaire$ efficacy $\times 1.1$. Typical output: 1100lm.

Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25° C, the LED lumen maintenance expectation according to IES TM-21-11 is: L90 (9k) >54,000 hrs (Reported methodology). L80 (9k) 145,000 hrs (Projected methodology).

Source Color

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 2 SDCM.

Controls

Available with the following integrated controls: Response daylight sensor (for single zone).

Wiring

Recessed: Optional flex whips are supplied in 6' lengths. Surface: Standard wiring configurations available.

Approvals

Certified to UL, CSA, and IES standards. City of Chicago Approved CCEA (housing option C). Certain versions without battery packs are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers (www.designlights.org/QPL).

Warranty

Five-year luminaire limited warranty including LED boards and driver.

USA: http://www.usa.lighting.philips.com/support/support/warranty

Canada: http://www.lighting.philips.ca/support/support/warranty

Environment


Rated for dry & damp locations in operating ambient temperatures of $0-25^{\circ}\mathrm{C}$ (32-77°F). Many luminaire components, such as reflectors, refractors, lenses, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility. Damage caused by sulfur, chlorine, petroleum based solution or other contaminants are not covered under warranty.


Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.

Options and Details


Mounting

Cross Section






Photometry - 3500K



0% Up / 100% Down



Candela Distribution

| Vertical | | Hori | zontal A | Angle | | Zonal |
|----------|-----|------|----------|-------|-----|--------|
| Angle | 0 | 22.5 | 45 | 67.5 | 90 | Lumens |
| 0 | 801 | 801 | 801 | 801 | 801 | 0 |
| 5 | 801 | 802 | 803 | 804 | 804 | 77 |
| 15 | 790 | 797 | 812 | 828 | 835 | 230 |
| 25 | 763 | 779 | 816 | 857 | 876 | 378 |
| 35 | 704 | 727 | 786 | 852 | 882 | 494 |
| 45 | 603 | 628 | 696 | 772 | 808 | 539 |
| 55 | 464 | 485 | 544 | 610 | 644 | 489 |
| 65 | 309 | 323 | 360 | 405 | 426 | 360 |
| 75 | 156 | 162 | 180 | 201 | 212 | 193 |
| 85 | 36 | 36 | 38 | 42 | 45 | 47 |
| 90 | 0 | 0 | 0 | 0 | 0 | 0 |
| 95 | 0 | 0 | 0 | 0 | 0 | 0 |
| 105 | 0 | 0 | 0 | 0 | 0 | 0 |
| 115 | 0 | 0 | 0 | 0 | 0 | 0 |
| 125 | 0 | 0 | 0 | 0 | 0 | 0 |
| 135 | 0 | 0 | 0 | 0 | 0 | 0 |
| 145 | 0 | 0 | 0 | 0 | 0 | 0 |
| 155 | 0 | 0 | 0 | 0 | 0 | 0 |
| 165 | 0 | 0 | 0 | 0 | 0 | 0 |
| 175 | 0 | 0 | 0 | 0 | 0 | 0 |
| 180 | 0 | 0 | 0 | 0 | 0 | 0 |
| | | | | | | |

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

| RCR | Ceiling: | | 8 | 0 | | | 70 | | | 50 | | 0 |
|-----|----------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| KCK | Wall: | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 50 | 30 | 10 | 0 |
| 0 | | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 111 | 111 | 111 | 100 |
| 1 | | 109 | 104 | 99 | 96 | 106 | 101 | 98 | 97 | 94 | 91 | 83 |
| 2 | | 98 | 90 | 83 | 77 | 96 | 88 | 82 | 85 | 79 | 75 | 69 |
| 3 | | 89 | 79 | 70 | 64 | 87 | 77 | 69 | 74 | 67 | 62 | 58 |
| 4 | | 82 | 69 | 60 | 53 | 79 | 68 | 60 | 65 | 58 | 52 | 49 |
| 5 | | 75 | 62 | 52 | 46 | 73 | 61 | 52 | 58 | 51 | 45 | 42 |
| 6 | | 69 | 55 | 46 | 40 | 67 | 54 | 46 | 52 | 45 | 39 | 36 |
| 7 | | 64 | 50 | 41 | 35 | 62 | 49 | 41 | 48 | 40 | 34 | 32 |
| 8 | | 59 | 45 | 37 | 31 | 58 | 45 | 36 | 43 | 36 | 30 | 28 |
| 9 | | 55 | 41 | 33 | 27 | 54 | 41 | 33 | 40 | 32 | 27 | 25 |
| 10 | | 52 | 38 | 30 | 25 | 50 | 38 | 30 | 37 | 29 | 24 | 22 |
| | | | | | | | | | | | | |

Avg. Luminance (cd/m2)

| Vertical | Horizontal Angle | | | | | |
|----------|------------------|------|------|--|--|--|
| Angle | 0 | 45 | 90 | | | |
| 55 | 2625 | 3082 | 3647 | | | |
| 65 | 2375 | 2766 | 3275 | | | |
| 75 | 1951 | 2252 | 2662 | | | |
| 85 | 1323 | 1431 | 1681 | | | |

Distribution Summary

| Hemisphere | 0% Up / 100% Down |
|-----------------------|-------------------|
| Spacing Along (0°) | 1.36 |
| Spacing Across (90 °) | 1.63 |



2'x2', 3000 lm CRI 90 3500K

Optical Performance

| Flux (lm) | 2806 |
|-----------------|--------|
| Efficacy (lm/W) | 86.3 |
| Power (W) | 32.5 |
| ССТ (К) | 3347 |
| CRI | 92 |
| R9 | 76 |
| х | 0.4158 |
| у | 0.3990 |
| Duv | 0.0010 |

Electrical Performance - 3500K

| Input Voltage | 120V | 277V | 347V |
|------------------------|-------|-------|-------|
| Input Power | 32.5W | 32.5W | 32.2W |
| Input Current | 0.28A | 0.13A | 0.10A |
| Power Factor | 0.982 | 0.890 | 0.961 |
| Total Harm. Distortion | 15.1% | 19.0% | 10.0% |



281 Hillmount Rd, Markham, ON, Canada L6C 2S3

Philips Lighting Canada Ltd.,

Tel. 800-668-9008