



Cubelite LED



LED Surface Luminaire



Cubelite LED

LED Surface Luminaire

A new, high performing LED surface luminaire delivering smooth diffuse light ideal for corridors, stairwells and vanity applications with the unparalleled energy efficiency of Philips LEDs.



Features

- Low profile 4-3/4" depth
- Up to 4700 lm per unit
- Individual or continuous row mountable
- Opal lens shields LED from view
- 50,000hr Rated Life (L₈₀)

Ordering Information

Family	Length	Lumens	Colour	Voltage	Driver	Lens
CSW	48	—				ZO
Cubelite	48 4' length (Nominal)	28 2800 lumens 47 4700 lumens (Nominal)	40 4000K 35 3500K	U Universal 120-277v 3 347v ¹	LAG LED driver DZT 0-10v dimming	ZO Opal lens

¹ Consult factory on availability.



Philips CFI
3015 Louis-Amos, Lachine, Québec, H8T 1C4
e. canlyte-info@philips.com
t: (514) 636-0670
w: www.canlyte.com

CSW48_PB_b January 17, 2013

Specifications are subject to change without notice.
© Koninklijke Philips Electronics N.V., 2013. All rights reserved.

