


Lytecaster 6 3/4", Flush Glass, Wet Location, Shower Trim

Page 1 of 1

Project:	Catalog No:	Mfg:
Location:	Fixture Type:	Qty:
Notes:		Lamps:



Ordering guide Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

Reflector Trim		Frame-In Kit — See Individual Frame-In Kit Specification Sheets							
1190	Flush Glass, Wet Location, Shower Trim	LED				Incandescent			
		Frame-In Kit	Installation Type	Lamping	Height	Frame-In Kit	Ceiling Type	Lamping	Height
		1101LED 1100LEDREM L56LED	Non-IC	LED	6 1/2"	1102P1	Non-IC	120W PAR38	6 1/2"
			Non-IC Remodeler			1103R	Non-IC Remodeler		
			Non-IC Retrofit			1100IC	IC	90W PAR38	7 5/16"
		Fluorescent				1100AICM	AirSeal IC		
		Frame-In Kit	Ceiling Type	Lamping	Height	1100DICM	Deep IC	75W PAR38	9 1/4"
		1101F18U Series	Uniframe Non-IC	(1) Triple 18W (GX24q-2)	5 3/4"	1100DAICM	Deep AirSeal IC		
		1101F18ICU/N	Performance IC	(1) Triple 18W (GX24q-2)	7 1/4"	1104ICX/N	AirSeal IC	60W PAR38	7 1/4"
						1104IC/N	AirSeal IC	45W PAR38	7 1/2"
				1104ICR	IC Remodeler				
				1104IC/N	Non-IC	100W PAR38	7 1/2"		
				1104ICR	Non-IC Remodeler				

Features

- Housing:** Hydroformed aluminum, .040 thk. min. Non-yellowing, gloss white powder coat finish for permanent reflectivity and surface protection.
- Trim Flange:** Frosted clear polycarbonate flange ring. Pull down and release for toolless relamping.
- Frame-In Kit:** (1102P1 standard frame shown) Other frames noted. See Frame-In Kit specification sheets for more details.
- Glass:** Pressed borosilicate glass textured diffuser. Smooth surface on exposed side for wipe down cleaning. Meets NEC® requirements for spas and hot tubs. May be installed less than 7' 6" above max water surface height. (NEC® is a registered trademark of the National Fire Protection Association.)

Labels

UL (Suitable for Wet Locations - Covered Ceilings only), I.B.E.W.