application

 Philips Capri 6" high efficiency CFL downlight for new construction. Provides broad uniform light distribution for general illumination. Ideal for areas that require long hours of continuous operation.

construction

- Ballast NE1 electronic ballast 120V, normal power factor
- Bar Hanger Pre-Installed BH-1 bar hangers telescope from 10.5 to 25 inches. Alignment holes to center fixture are located at 10.5" and 25" centers. Bar hanger is equipped with heavy-duty fluted nails. Interlocking support tabs provide smooth adjustment on bar hangers.
- Plaster Frame Precision die-stamped plaster frame of galvanized steel. Mounting frame accommodates ceiling materials from 1/2" to 1-3/8" thick.
- Reflector Reflectors include universal feature allowing trim to be used on Phlips Lightolier CPlus Title 24 IC/Airseal rated high efficacy compact fluorescent downlights and select Philips Lightolier incandescent 6 inch IC/AirSeal™ rated downlights.
- Baffle Precision spun .04 aluminum with deep grooves to reduce aperture glare. Non-reflective matte black or white finish.
- Socket One vertically mounted socket orients lamp at optical focal plane of reflector for precise optics.
- Junction Box Extra large 32 cubic inch .063" galvanized steel with snap on cover and ground wire riveted to frame. Approved for Through Branch Circuit Wiring with up to 3 #12 guage AWG conductors. Knockouts for 1/2" and 3/4" conduit and 4 romex pry-outs with strain relief.

listings

- cULus Listing cULus Listed for damp locations and through branch wiring (4in/4 out). SHRICW is listed for wet locations. California Title 24 Compliant.
- AirSeal™ Luminaire is AirSeal™ rated meeting ASTM E283 limiting passage of air through housing to no more than 2.0 CFM at 75 Pascals.AirSeal™ housing meets restricted airflow requirements of Washington State Energy Code (W.S.E.C.) and International Energy Conservation Code (I.E.C.C.). Luminaire supplied with preinstalled gasket to ensure AirSeal™ installation.

PR26ASICNBNE1

Philips Lightolier C-Plus Recessed Downlight

6" CFL CPlus Recessed AirSeal™/IC Rated Vertical-Socket Supporting Downlight



C	_:C:	'- D -	£
SDE	ecifier	s Ke	eference

Project

Туре


Model No.

Comments





Green Choice: PR26ASICNBNE1-RB30W





RB30W - Grooved White Baffle


RB30 – Grooved Black Baffle
RBC30WM – Cone Grooved White Baffle


 $\textbf{RBA100CLR}-\mathsf{Clear}\;\mathsf{Cone}\,\mathsf{White}\;\mathsf{Baffle}$

SHR61CW – White Regressed Shower



dimensions





trims



RB30W Full White Baffle Socket Supporting 7-1/16" O.D. (179 mm)

26W Triple Tuble



RC30C Clear Cone (shown) RC30W White Cone Socket Supporting 7-1/16" O.D. (179 mm)

26W Triple Tuble



RBC30WM Full White Baffle w/Torsion Springs Socket Supporting 7-1/16" O.D. (179 mm)

26W Triple Tuble



RBA100CLR Clear Cone Socket Supporting 7-1/16" O.D. (179 mm)

26W Triple Tuble



SHR16IC Regressed Glass Shower Light, Wet Location 8" O.D. (203 mm)

26W Triple Tuble



Some luminaires use fluorescent or high intensity discharge (HID) lamps that contain small amounts of mercury. Such lamps are labeled, "Contain Mercury" and/or the symbol "HG". Lamps that contain mercury must be disposed of in accordance with local requirements. Information regarding lamp recycling and disposal can be found at www.lamprecycle.org



Hg

© 2013 Koninklijke Philips N.V. All rights reserved. Specifications are subject to change without notice. www.philips.com/luminaires

PR26ASICNBNE1 02/14 page 2 of 2

Philips Lighting North America Corporation 200 Franklin Square Drive Somerset, NJ 08873 Phone: 855-486-2216

Philips Lighting Company 281 Hillmount Road Markham ON, Canada L6C 2S3 Phone: 800-668-9008