



PHILIPS
Recessed spot light
80083 4" 8W 27K Silver
silver
LED



80083/27/66

Essential lighting for a bright home

Complete your home in style with the Philips Essalu LED downlight Silver. Made of high quality diecast aluminum, it is accented with decorative ring and incorporates long lasting LED light source and high quality anti glare diffuser.

Light effect

- Even light distribution

Long lifespan

- Extremely long life 20,000 hours

Energy saving

- Built-in LED, as part of the system

Premium quality

- Die-casted aluminum for a premium look and feel

PHILIPS

Highlights

Even light distribution



Integrated LED light source



Extremely long life



A light source you can trust. With integrated LED light source, you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

Premium materials



A light source you can trust. Philips LED lights offer an extremely long-life of at least 20,000 hours (which equals 20 years on basis of an average use of 3 hours / day with an amount of at least of 13,000 on/off switching cycles). It feels so comfortable to think that you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

Specifications

Design and finishing

- Color: silver
- Material: aluminium

Extra feature/accessory incl.

- Diffused light effect: Yes
- LED integrated: Yes
- Photometric data available: Yes
- Protection sleeve included: Yes
- Resistant high quality material: Yes

Miscellaneous

- Especially designed for: Living- & Bedroom
- Style: Functional
- Type: Recessed spot light
- EyeComfort: No

Product dimensions & weight

- Cut out length: 12.5 cm
- Cut out width: 12.5 cm
- Length: 13.9 cm
- Net weight: 0.230 kg
- Recessed distance: 8.0 cm
- Width: 7.7 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Bulb technology: LED, 230 V
- Light color: warm white
- Mains power: Range 100 V – 240 V, 50–60 Hz
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Number of bulbs: 32
- Wattage bulb included: 0.5 W
- Maximum wattage replacement bulb: 0.5 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II – double insulated

Packaging dimensions & weight

- SAP EAN/UPC – Piece: 6947830425525
- EAN/UPC – Case: 6947830472321
- Height: 14.8 cm
- SAP Gross Weight EAN (Piece): 0.297 kg
- Weight: 0.297 kg
- Net Weight (Piece): 0.229 kg
- SAP Height (Piece): 148.000 mm
- SAP Length (Piece): 85.000 mm
- SAP Width (Piece): 143.000 mm
- Width: 8.5 cm
- Length: 14.3 cm



Issue date: 2019-07-31
Version: 0.298

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com