

# Upgrade with versatile style

Whether you are looking to beautify or add a sense of security and well-being to your outdoor space, the highly configurable Philips Hadco LED refractive post tops paired with the latest LumiLock light engine GX4 will definitely help you achieve your goals. A multitude of exterior luminaire styles allow you to create promenades and areas exuding timeless, historical charm both day and night. The configurable LED light engine GX4 is an ideal alternative to HID sources, providing you with significant energy savings, and more choices for light levels, optics and controls.

- Luminaires are available with a variety of cages, finials, roofs, pods and colors to customize the project along with various poles and brackets.
- Provides a quick and simple retrofit solution for existing Philips Hadco RL and CL Series luminaires while maintaining excellent light levels.
- Field capabilities to change distribution from type 3 and type 5 optics to adapt when needed.
- Variety of drive current and optic choices to provide the right amount of light where you need it.
- Variety of LED color choices in warm and neutral CCTs.
- Variety of dimming and control choices to maximize energy savings and help you prepare for the future.
- Includes Service Tag, Philips innovative way to provide assistance throughout the life of the product.  
For more details visit: [philips.com/servicetag](https://philips.com/servicetag)



© 2018 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

PHc-1701BN\_GX4-Bulletin 01/18

Philips Lighting  
North America Corporation  
200 Franklin Square Drive  
Somerset, NJ 08873  
Tel. 855-486-2216

Philips Lighting Canada Ltd.  
281 Hillmount Rd.  
Markham, ON,  
Canada L6C 2S3  
Tel. 800-668-9008

**PHILIPS**  
**HADCO**

Urban

Refractive post tops

with LumiLock LED engine



# Versatility from the inside out





## RL34/RL54

### LED refractive post top

Lumen range: 3,024 - 12,454  
Wattage range: 39 - 104  
Efficacy range: 70 - 132

Wide body styles

RL34BABA   RL34LGIN   RL34ABNN   RL34BBBN   RL34BCEA   RL34ADEB

### Simple retrofit and upgrade installation

Upgrading a Philips Hadco luminaire from a traditional lamp source to today's LED energy saving technology doesn't have to mean a replacement of an entire luminaire. Philips Hadco's LumiLock provides a quick retrofit solution. Just twist out the existing LumiLock two part assembly and replace it with the LumiLock LED GX4 system. That's it!



## RL32/RL52

### LED refractive post top

Lumen range: 3,560 - 12,399  
Wattage range: 39 - 104  
Efficacy range: 82 - 132

Narrow body styles

RL52BABA   RL52AA(custom)   RL52BDGC   RL52ABNN   RL52BAEA   RL52GBBN

### Asymmetric or symmetric? With LumiLock LED, you have both.

It may happen that the site environment changed or even your needs evolved, thanks to the ultimate versatility system that allows the LumiLock LED light engine GX4 to quickly be converted in the field from symmetric to asymmetric distribution or vice-versa to adapt when needed.

### Versatility in light - Short optics/Wide optics

The new Lumilock LED light engine in the RL and CL Series now includes even more selection beyond the typical type 3 or type 5 distributions. A new option includes the ability to choose between a Short or Wide optic distribution. Choose the Short optic if the requirement is to place more light under the pole and maximize uniformity, or use the Wide optic to maximize pole spacings.

Short optics   Wide optics



## CL32/CL52

### LED refractive post top

Lumen range: 3,560 - 12,399  
Wattage range: 39 - 104  
Efficacy range: 82 - 132

Contemporary narrow body styles

CL52MHLA   CL52MKLN   CL52PDNN   CL52PJKN   CL52PKLN   CL52RJLA

### From simple dimming to state of the art connected lighting solutions

Further versatility can be achieved by incorporating our standalone and connected outdoor LED lighting solutions. From dimming that saves energy, to real-time alerts that enable quicker and more effective maintenance response, Philips Hadco LED refractive post tops with connected lighting solutions provide even greater savings and adaptability to your project requirements.

Because these post tops are renowned to offer the timeless historical aesthetic for that hometown and traditional feel for urban spaces, we now provide the option to order a 5 or 7 pin receptacle inside the luminaire so there is no need for external hardware or components detracting from the decorative aesthetic of the luminaire.