



## Declaration of Conformity

**Philips Color Kinetics**

3 Burlington Woods Drive  
Burlington, MA 01803, USA

Year in which CE Mark was first affixed: 2012

**Declare responsibility for the product(s):**

<b>Product Range:</b>	eW Cove MX Powercore eColor Cove MX Powercore eW FUSE Powercore eColor FUSE Powercore
<b>Product Code:</b>	523-000050-XX 223-000050-XX 523-000065-XX 223-000065-XX 999-016XXX-XX 999-039XXX-XX

**The designated product(s) are in conformity with the essential requirements of the following European Directives and harmonized standards:**

**Low Voltage Directive (LVD), 2006/95/EC**

- EN 60598-1:2008 + A11:2009
- EN 60598-2-1:1989
- EN 61347-1:2008
- EN 61347-2-13:2006
- EN 62471:2008
- EN 62493:2010

**Electromagnetic compatibility Directive (EMC), 2004/108/EC**

- EN 55015:2006 + A1:2007 + A2:2009
- EN 61000-3-2:2006 + A1:2009 + A2:2009
- EN 61000-3-3:2008
- EN 61547:2009

**Restriction on Hazardous Substances Directive (RoHS), 2011/65/EU**

- EN 50581:2012

**December 12, 2012  
Burlington, MA USA**

**James Anderson**  
Director of Quality Assurance  
Philips Color Kinetics/Philips Solid-State Lighting Solutions

Annex

Date: December 12, 2012

Annex to original Mfrs Declaration of Conformity MDC for eW Cove MX Powercore, eColor Cove MX Powercore, eW FUSE Powercore, eColor FUSE Powercore Luminaries dated December 12, 2012.

Brand Name: Philips Color Kinetics

All Models/Materials noted below are also covered by the above referenced MDC, Material code (12 nc):

Material	Material Description	CK P/N
910503701106	BCX450 10xLED-HB/BL 100-240V WB MSR	223-000050-02
910503701112	BCX421 10xLED-HB/RD 100-277V MB	223-000050-08
910503701113	BCX421 10xLED-HB/GN 100-277V MB	223-000050-09
910503701114	BCX421 10xLED-HB/BL 100-277V MB	223-000050-10
910503701115	BCX421 10xLED-HB/AM 100-277V MB	223-000050-11
910503701730	BCX421 10xLED-HB/RD 100-277V WB	223-000050-12
910503701731	BCX421 10xLED-HB/GN 100-277V WB	223-000050-13
910503701732	BCX421 10xLED-HB/BL 100-277V WB	223-000050-14
910503701733	BCX421 10xLED-HB/AM 100-277V WB	223-000050-15
910503702591	BCX421 10xLED-HB/RD 100-277V L1220 WB	223-000050-16
910503702592	BCX421 10xLED-HB/GN 100-277V L1220 WB	223-000050-17
910503702593	BCX421 10xLED-HB/BL 100-277V L1220 WB	223-000050-18
910503702594	BCX421 10xLED-HB/AM 100-277V L1220 WB	223-000050-19
910503702595	BCX421 10xLED-HB/RD 100-277V L1220 MB	223-000050-20
910503702596	BCX421 10xLED-HB/GN 100-277V L1220 MB	223-000050-21
910503702597	BCX421 10xLED-HB/BL 100-277V L1220 MB	223-000050-22
910503702598	BCX421 10xLED-HB/AM 100-277V L1220 MB	223-000050-23
910503701676	LS518X 10 x LEDs-HB/BL 100-277V NB WH	223-000065-02
910503701680	LS518X 10 x LEDs-HB/BL 100-277V MB WH	223-000065-06
910503701709	LS518X 10xLED-HB/RD 100-277V NB WH	223-000065-08
910503701710	LS518X 10xLED-HB/GN 100-277V NB WH	223-000065-09
910503701711	LS518X 10xLED-HB/BL 100-277V NB WH	223-000065-10
910503701712	LS518X 10xLED-HB/AM 100-277V NB WH	223-000065-11
910503701713	LS518X 10xLED-HB/RD 100-277V MB WH	223-000065-12
910503701714	LS518X 10xLED-HB/GN 100-277V MB WH	223-000065-13
910503701715	LS518X 10xLED-HB/BL 100-277V MB WH	223-000065-14
910503701716	LS518X 10xLED-HB/AM 100-277V MB WH	223-000065-15
910503702599	LS518X 10xLED-HB/RD 100-277V L1220 NB	223-000065-16
910503702601	LS518X 10xLED-HB/GN 100-277V L1220 NB	223-000065-17
910503702602	LS518X 10xLED-HB/BL 100-277V L1220 NB	223-000065-18
910503702603	LS518X 10xLED-HB/AM 100-277V L1220 NB	223-000065-19
910503702604	LS518X 10xLED-HB/RD 100-277V L1220 MB	223-000065-20
910503702605	LS518X 10xLED-HB/GN 100-277V L1220 MB	223-000065-21
910503702606	LS518X 10xLED-HB/BL 100-277V L1220 MB	223-000065-22
910503702607	LS518X 10xLED-HB/AM 100-277V L1220 MB	223-000065-23
910503700979	BCX416 10xLED-HB-2700 100-277V MB	523-000050-01
910503700980	BCX416 10xLED-HB/WW-2700 100-277V 120	523-000050-02
910503700983	BCX416 10xLED-HB-3000 100-277V MB	523-000050-05
910503700984	BCX416 10xLED-HB/WW-3000 100-277V 120	523-000050-06
910503700987	BCX416 10xLED-HB-3500 100-277V MB	523-000050-09
910503700988	BCX416 10xLED-HB/NW-3500 100-277V 120	523-000050-10

910503700991	BCX416 10xLED-HB-4000 100-277V MB	523-000050-13
910503700992	BCX416 10xLED-HB/NW-4000 100-277V 120	523-000050-14
910503701725	BCX416 18xLED-HB-2200 100-277V WB	523-000050-16
910503701726	BCX416 10xLED-HB/2700 100-277V WB	523-000050-17
910503701727	BCX416 10xLED-HB/3000 100-277V WB	523-000050-18
910503701728	BCX416 10xLED-HB/3500 100-277V WB	523-000050-19
910503701729	BCX416 10xLED-HB/4000 100-277V WB	523-000050-20
910503702610	BCX416 72xLED-HB/WW-2200 100-277V WB	523-000050-21
910503702540	BCX416 10xLED-HB/2700 100-277V L1220 WB	523-000050-22
910503702611	BCX416 10xLED-HB/3000 100-277V L1220 WB	523-000050-23
910503702682	BCX416 10xLED-HB/3500 100-277V L1220 WB	523-000050-24
910503702753	BCX416 10xLED-HB/4000 100-277V L1220 WB	523-000050-25
910503702614	BCX416 10xLED-HB/2700 100-277V L1220 MB	523-000050-26
910503702615	BCX416 10xLED-HB/3000 100-277V L1220 MB	523-000050-27
910503702616	BCX416 10xLED-HB/3500 100-277V L1220 MB	523-000050-28
910503702541	BCX416 10xLED-HB/4000 100-277V L1220 MB	523-000050-29
910503701653	LS515X LED5/827 100-277V 10 WH	523-000065-00
910503701654	LS515X LED5/830 100-277V 10 WH	523-000065-01
910503701655	LS515X LED5/835 100-277V 10 WH	523-000065-02
910503701656	LS515X LED5/840 100-277V 10 WH	523-000065-03
910503701657	LS515X LED5/827 100-277V 30 WH	523-000065-04
910503701658	LS515X LED5/830 100-277V 30 WH	523-000065-05
910503701659	LS515X LED5/835 100-277V 30 WH	523-000065-06
910503701660	LS515X LED5/840 100-277V 30 WH	523-000065-07
910503701717	LS515X LED5/2700 100-277V NB WH	523-000065-08
910503701718	LS515X LED5/3000 100-277V NB WH	523-000065-09
910503701719	LS515X LED5/3500 100-277V NB WH	523-000065-10
910503701720	LS515X LED5/4000 100-277V NB WH	523-000065-11
910503701721	LS515X LED5/2700 100-277V MB WH	523-000065-12
910503701722	LS515X LED5/3000 100-277V MB WH	523-000065-13
910503701723	LS515X LED5/3500 100-277V MB WH	523-000065-14
910503701724	LS515X LED5/4000 100-277V MB WH	523-000065-15
910503702617	LS515X LED5/2700 100-277V L1220 NB	523-000065-16
910503702618	LS515X LED5/3000 100-277V L1220 NB	523-000065-17
910503702619	LS515X LED5/3500 100-277V L1220 NB	523-000065-18
910503702620	LS515X LED5/4000 100-277V L1220 NB	523-000065-19
910503702621	LS515X LED5/2700 100-277V L1220 MB	523-000065-20
910503702622	LS515X LED5/3000 100-277V L1220 MB	523-000065-21
910503702623	LS515X LED5/3500 100-277V L1220 MB	523-000065-22
910503702624	LS515X LED5/4000 100-277V L1220 MB	523-000065-23



James Anderson