






Project:	
Spec Type:	
Catalog No:	3900LxKL
Qty	
Line Notes:	

TruGroove recessed delivers unrivaled performance and a truly innovative design – making a definitive statement in any architectural space. TruGroove recessed corners provide endless opportunities for creative freedom with geometric patterns in walls and ceilings.

Ordering guide



- * Nominal values within a range. Consult photometry data for CRI, color temp, lumens & distribution of chosen configuration.
- † Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.
- ≈ Available in continuous run lengths from 6ft in steps as small as 1/8in for 1500lm/4ft & 2200lm/4ft symmetric configurations.
- ≈ All 3000lm/4ft, 4000lm/4ft and asymmetric configurations can be specified in 1ft steps.

Ceiling Trims Integrated Controls Please indicate with check mark. Response Daylight Single Zone (DS) SpaceWise DT Occupancy & Daylight Sensor (SZ) T-Grid Drywall Trimless Drywall Trim







Flush Silk Lens 1500 lm/4ft, 3000/3500/4000K

Optical System

Performance version: White light emitted from the LED sources is internally reflected and exits through the optical lens assembly. This assembly contains acrylic extrusion profiles to retain a layer of MesoOptics film, creating both an uninterrupted continuum of light and an optical batwing distribution.

Definition version: Light passes through a diffuse white acrylic lens to deliver a highly uniform luminous continuum.

Finish

Extruded aluminum trim and die-cast endplates coated with electrostatically applied and thermally cured polyester. Powder coat paint finish. White sensors only.

Housing

Die-formed 20 gauge cold-rolled steel. Multiple upper wire entrances available for continuous row mounting of fixtures.

Weight

Maximum 3.5lb/ft.

Electrical

Factory pre-wired to section ends with quick-wire connectors.

Wall Options

Wall mounted luminaires are only available with the Drywall Trimless ceiling / trim option. A continuous ceiling to wall pattern with an inside corner can use a different ceiling / trim option on the ceiling if required.

Regressed lens and 4000 lm/4ft configurations are not available for wall mounting.

Standard Drivers

Philips Advance Xitanium 0-10V, 1-100%. Philips Advance Xitanium Sensor Ready, 5-100%. Class 2 rated output. Consult Philips Ledalite for other available drivers.

Standard Battery Pack

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output: 1100lm.

Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C in non-insulated contact applications the LED lumen maintenance expectation according to IES TM-21-11 is:

L₉₀ (10k) >60,000 hrs (**Reported** methodology) L₈₀ (10k) 120,000 hrs (**Calculated** methodology).

Source Color

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 2 SDCM.

Controls

Certain configurations available with: Response Daylight Sensors SpaceWise DT Occupancy & Daylight Sensors w/ advanced grouping & Dwell Time.

*SpaceWise DT commissioning is via a compatible Android phone and Philips Field App. Compatible wireless dimming wall switches are available for dimming. 347V is not available as a standard option. For more information, please refer to www.philips.com/spacewise

Mounting

Mounting brackets on housing sides support T-Grid installation. 1/16" diameter aircraft cable with self-locking, tamper-resistant, miniature cable gripper provides vertical adjustment for drywall. Aircraft cable, crimp and gripper independently tested to meet stringent safety requirements.

Compatible with 4" Armstrong TechZone ceiling grid.

Joints

Self-aligning joining system with hands-free pre-joining wire access.

Approvals

Certified to UL, CSA and IES standards. Insulation Contact (IC) rated. Most symmetric, flush lens versions between 1500-3000lm/4ft in 3500K and 4000K are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers under DLC family code WWWBXQ (www.designlights.org/QPL).

Warranty

Five-year luminaire limited warranty including LED boards and driver.

USA: http://www.usa.lighting.philips.com/support/support/warranty


Canada: http://www.lighting.philips.ca/support/support/warranty


Environment

Rated for dry & damp locations in operating in ambient temperatures of 25°C. Many luminaire components, such as reflectors, refractors, lenses, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility. Damage caused by sulfur, chlorine, petroleum based solution or other contaminants are not covered under warranty


Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.

Corner details and dimensions





Nominal Length	Housing	Lens	Mounting Points	Trim - T-Grid	Trim - Drywall Trimless	Trim - Drywall Trim
2x2ft Flat	25.7"/653mm	N/A	23.6"/600mm	25.9"/658mm	27.1°/689mm	26.3"/667mm




Nominal	Trim-Drywall
Length	Trimless
2x2ft Outside	26.8"/681mm

Flush Silk Lens


1500 lm/4ft, 3000/3500/4000K


Ceiling Types



Module Details & Dimensions


Standalone






Standalone							
Nominal	Housing	Lens	Mounting Points	Trim -T-Grid	Trim - Drywall Trimless	Trim - Drywa ll Trim	
2ft	23.9~/607mm	23.0~/584mm	23.4"/594mm	23.8"/605mm	26.4"/670mm	24.5"/622mm	
3ft	35.9"/912mm	35.0"/889mm	35.4"/899mm	35.8"/909mm	38.4"/975mm	36.5"/927mm	
4ft	47.9"/1217mm	47.0°/1194mm	47.4"/1204mm	47.8"/1214mm	50.4″/1280mm	48.5"/1232mm	
5ft	59.9"/1521mm	59.0~/1499mm	59.4″/1509mm	59.8"/1519mm	62.4"/1585mm	60.5″/1537mm	
6ft	71.9"/1826mm	71.0°/1803mm	71.4"/1814mm	71.8"/1824mm	74.4"/1889mm	72.5″/1841mm	
8ft	95.9"/2436mm	95.0"/2413mm	95.4″/2423mm	95.8"/2433mm	98.4"/2499mm	96.5″/2451mm	


Mid-Run



Mid-Run					
Nominal	Housing & Lens	Mounting Points			
2ft	24.0~/610mm	23.2"/589mm			
3ft	36.0~/914mm	35.2"/894mm			
4ft	48.0°/1219mm	47.2"/1199mm			
5ft	60.0"/1524mm	59.2″/1504mm			
6ft	72.0"/1829mm	71.2"/1809mm			
8ft	96.0"/2438mm	95.2″/2418mm			
Incremental	L	L-0.8"			

End-Run








End-Run						
Nominal	Housing		Mounting Points	Trim -T-Grid	Trim - Drywall Trimless	Trim - Drywall Trim
2ft	24.0~/610mm	23.5"/597mm	23.2″/589mm	23.9"/606mm	25.7"/653mm	24.8"/629mm
3ft	36.0°/914mm	35.5"/901mm	35.2"/894mm	35.9~/910mm	37.7"/957mm	36.7"/933mm
4ft	48.0°/1219mm	47.5"/1206mm	47.2"/1199mm	47.9″/1215mm	49.7″/1262mm	48.7"/1238mm
5ft	60.0"/1524mm	59.5"/1511mm	59.2"/1504mm	59.9"/1520mm	61.7"/1567mm	60.7″/1543mm
6ft	72.0"/1829mm	71.5~/1816mm	71.2"/1809mm	71.9"/1825mm	73.7"/1872mm	72.8"/1848mm
8ft	96.0"/2438mm	95.5"/2425mm	95.2"/2418mm	95.8"/2434mm	97.7″/2481mm	96.7"/2457mm
Incremental	L	L-0.5"	L-0.8"	L-0.1"	L+1.7"	L+0.75"

Flush Silk Lens 1500 lm/4ft, 3000/3500/4000K

Photometry @ CRI>80, 3500K







Candela Distribution

Vertical			Zonal			
Angle	0	22.5	45	67.5	90	Lumens
0	558	558	558	558	558	0
5	546	552	556	559	558	53
15	525	531	536	540	539	151
25	484	491	494	496	496	227
35	427	434	436	435	434	271
45	357	362	363	361	360	278
55	277	280	280	277	276	249
65	189	192	190	189	188	188
75	99	100	100	100	100	106
85	22	22	24	25	26	28
90	0	0	0	0	0	0
95	0	0	0	0	0	0
105	0	0	0	0	0	0
115	0	0	0	0	0	0
125	0	0	0	0	0	0
135	0	0	0	0	0	0
145	0	0	0	0	0	0
155	0	0	0	0	0	0
165	0	0	0	0	0	0
175	0	0	0	0	0	0
180	0	0	0	0	0	0

Values per 4ft unit

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

ncn	Ceiling:		8	0			70			50		0
RCR	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		119	119	119	119	116	116	116	111	111	111	100
1		109	104	100	96	106	102	98	97	94	91	84
2		99	91	84	78	96	89	83	85	80	75	70
3		90	80	71	65	88	78	70	75	69	63	59
4		83	71	62	55	80	69	61	67	60	54	50
5		76	63	54	47	74	62	53	60	52	47	43
6		70	57	48	41	68	56	47	54	46	41	38
7		65	51	43	37	63	51	42	49	42	36	34
8		61	47	38	33	59	46	38	45	38	32	30
9		57	43	35	29	55	43	35	41	34	29	27
10		53	40	32	27	52	39	32	38	31	26	24

Avg. Luminance (cd/m2)

Vertical	H	orizontal An	gle
Angle	0	45	90
55	5191	5245	5179
65	4820	4848	4781
75	4112	4153	4174
85	2654	2926	3173

Distribution

Hemisphere	0% Up / 100% Down			
Glare Control	Meets RP-1-12 recommendations for VDT-Critical spaces			
Spacing Along (0°)	1.22			
Spacing Across (90°)	1.24			

Flush Silk Lens 1500 lm/4ft, 3000/3500/4000K

Optical Performance @ 120V

Nominal Spec:	830	835	840
Flux (lm)	1495	1551	1557
Efficacy (lm/W)	106.0	110.0	111.2
Power (W)	14.1	14.1	14.0
CCT (K)	3040	3437	3948
CRI	84	82	84
R9	16	10	14
x	0.4334	0.4097	0.3836
У	0.4017	0.3945	0.3813
Duv	0.0006	0.0007	0.0013

Electrical Performance @ CRI>80, 3500K

Input Voltage	120V	277V	347V
Input Power	14.1W	14.3W	14.7W
Input Current	0.12A	0.05A	0.04A
Power Factor	0.990	0.940	0.946
Total Harm. Distortion	11.3%	15.4%	15.5%

Tested values – contact technical support for rated values. Off-state power zero unless certain controls are specified.

With SpaceWise DT, standby power <0.5W (120V) or <0.8W (277V).

