



Declaration of Conformity

We, Philips Lighting

I.B.R.S./C.C.R.I. /Numéro 10461
5600 VB Eindhoven, The Netherlands

Year in which CE Mark was first affixed: 2012

Declare under our responsibility for the products:

Product Range:	eW Cove MX Powercore * eW FUZE Powercore * eColor Cove MX Powercore * eColor FUZE Powercore * EvenBalance Powercore * LED Luminaires *1FT version
Product Code:	523-000050-xx 523-000065-xx 223-000050-xx 223-000065-xx 523-000099-xx 999-016xxx-xx 999-039xxx-xx 999-064xxx-xx

The designated products are in conformity with the essential requirements of the following European Directives and harmonized standards:

Low Voltage Directive (LVD), 2014/35/EU

- EN 60598-1:2015
- EN 60598-2-1:1989
- EN 61347-1:2008 + A1:2011 + A2:2013
- EN 61347-2-13:2014
- EN 62471:2008
- EN 62493:2010

Electromagnetic compatibility Directive (EMC), 2014/30/EU

- EN 55015:2013
- EN 61000-3-2:2014
- EN 61000-3-3:2013
- EN 61547:2009

Restriction of the use of certain Hazardous Substances in electrical and electronic equipment Directive (RoHS), 2011/65/EU

- EN 50581:2012

May 05, 2016
Burlington, MA USA

Raymond Spiewak
Sr. Manager, QA
Philips Color Kinetics/Philips Lighting North America Corporation
3 Burlington Woods Drive
Burlington, MA 01803, USA

Annex

Date: **May 05, 2016**

Annex to original Mfrs Declaration of Conformity MDC for eW Cove MX Powercore, eW FUSE Powercore, eColor Cove MX Powercore, eColor Fuse Powercore, EvenBalance Powercore dated May 05, 2016.

Brand Name: Philips Color Kinetics

All Models/Materials noted below are also covered by the above referenced MDC, Material code (12 nc):

Material	Material Description	CK P/N
910503701106	BCX450 10xLED-HB/BL 100-240V WB MSR	223-000050-02
910503701112	BCX421 10xLED-HB/RD 100-277V MB	223-000050-08
910503701113	BCX421 10xLED-HB/GN 100-277V MB	223-000050-09
910503701114	BCX421 10xLED-HB/BL 100-277V MB	223-000050-10
910503701115	BCX421 10xLED-HB/AM 100-277V MB	223-000050-11
910503701730	BCX421 10xLED-HB/RD 100-277V WB	223-000050-12
910503701731	BCX421 10xLED-HB/GN 100-277V WB	223-000050-13
910503701732	BCX421 10xLED-HB/BL 100-277V WB	223-000050-14
910503701733	BCX421 10xLED-HB/AM 100-277V WB	223-000050-15
910503700980	BCX416 10xLED-HB/WW-2700 100-277V 120	523-000050-02
910503700983	BCX416 10xLED-HB-3000 100-277V MB	523-000050-05
910503700984	BCX416 10xLED-HB/WW-3000 100-277V 120	523-000050-06
910503700987	BCX416 10xLED-HB-3500 100-277V MB	523-000050-09
910503700988	BCX416 10xLED-HB/NW-3500 100-277V 120	523-000050-10
910503700991	BCX416 10xLED-HB-4000 100-277V MB	523-000050-13
910503700992	BCX416 10xLED-HB/NW-4000 100-277V 120	523-000050-14
910503701725	BCX416 18xLED-HB-2200 100-277V WB	523-000050-16
910503701726	BCX416 10xLED-HB/2700 100-277V WB	523-000050-17
910503701727	BCX416 10xLED-HB/3000 100-277V WB	523-000050-18
910503701728	BCX416 10xLED-HB/3500 100-277V WB	523-000050-19
910503701729	BCX416 10xLED-HB/4000 100-277V WB	523-000050-20
910503704153	BCX416 18xLED/2700 100-277V 305MM 8W WB	523-000050-30
910503704154	BCX416 18xLED/3000 100-277V 305MM 8W WB	523-000050-31
910503704155	BCX416 18xLED/3500 100-277V 305MM 8W WB	523-000050-32
910503704156	BCX416 18xLED/4000 100-277V 305MM8W WB	523-000050-33
910503704157	BCX416 18xLED/2700 100-277V 305MM 8W WB	523-000050-34
910503704158	BCX416 18xLED/3000 100-277V 305MM 8W WB	523-000050-35
910503704159	BCX416 18xLED/3500 100-277V 305MM 8W WB	523-000050-36
910503704160	BCX416 18xLED/4000 100-277V 305MM 8W WB	523-000050-37
912400130177	BCX416 10xLED-HB-2200 100-277V WB	523-000050-62
910503701676	LS518X 10 x LEDs-HB/BL 100-277V NB WH	223-000065-02
910503701709	LS518X 10xLED-HB/RD 100-277V NB WH	223-000065-08
910503701710	LS518X 10xLED-HB/GN 100-277V NB WH	223-000065-09
910503701711	LS518X 10xLED-HB/BL 100-277V NB WH	223-000065-10
910503701712	LS518X 10xLED-HB/AM 100-277V NB WH	223-000065-11
910503701713	LS518X 10xLED-HB/RD 100-277V MB WH	223-000065-12
910503701714	LS518X 10xLED-HB/GN 100-277V MB WH	223-000065-13
910503701715	LS518X 10xLED-HB/BL 100-277V MB WH	223-000065-14
910503701716	LS518X 10xLED-HB/AM 100-277V MB WH	223-000065-15
910503701653	LS515X LED5/827 100-277V 10 WH	523-000065-00
910503701654	LS515X LED5/830 100-277V 10 WH	523-000065-01
910503701655	LS515X LED5/835 100-277V 10 WH	523-000065-02
910503701656	LS515X LED5/840 100-277V 10 WH	523-000065-03
910503701657	LS515X LED5/827 100-277V 30 WH	523-000065-04

910503701658	LS515X LED5/830 100-277V 30 WH	523-000065-05
910503701659	LS515X LED5/835 100-277V 30 WH	523-000065-06
910503701660	LS515X LED5/840 100-277V 30 WH	523-000065-07
910503701717	LS515X LED5/2700 100-277V NB WH	523-000065-08
910503701718	LS515X LED5/3000 100-277V NB WH	523-000065-09
910503701719	LS515X LED5/3500 100-277V NB WH	523-000065-10
910503701720	LS515X LED5/4000 100-277V NB WH	523-000065-11
910503701721	LS515X LED5/2700 100-277V MB WH	523-000065-12
910503701722	LS515X LED5/3000 100-277V MB WH	523-000065-13
910503701723	LS515X LED5/3500 100-277V MB WH	523-000065-14
910503701724	LS515X LED5/4000 100-277V MB WH	523-000065-15
910503704161	LS515X LED5/2700 100-277V 305MM 8W NB	523-000065-24
910503704162	LS515X LED5/3000 100-277V 305MM 8W NB	523-000065-25
910503704163	LS515X LED5/3500 100-277V 305MM 8W NB	523-000065-26
910503704164	LS515X LED5/4000 100-277V 305MM 8W NB	523-000065-27
910503704165	LS515X LED5/2700 100-277V 305MM 8W MB	523-000065-28
910503704166	LS515X LED5/3000 100-277V 305MM 8W MB	523-000065-29
910503704167	LS515X LED5/3500 100-277V 305MM 8W MB	523-000065-30
910503704168	LS515X LED5/4000 100-277V 305MM 8W MB	523-000065-31
912400134211	LS550L 2700 L305 NB	523-000099-00
912400134212	LS550L 3000 L305 NB	523-000099-01
912400134213	LS550L 3500 L305 NB	523-000099-02
912400134214	LS550L 4000 L305 NB	523-000099-03
912400134219	LS550L 2700 L305 MB	523-000099-08
912400134220	LS550L 3000 L305 MB	523-000099-09
912400134221	LS550L 3500 L305 MB	523-000099-10
912400134222	LS550L 4000 L305 MB	523-000099-11
910503700973	ZCX416 C3050P WH	108-000047-01
910503700976	ZCX416 C305P-M-F WH	108-000048-02
910503700977	ZCX416 C1525P-M-F WH	108-000048-03
910503701787	ZCX450 RA L1220 WH	120-000124-00



Raymond Spiewak