

PHILIPS

Incandescent
appliance bulb

Speciality

25 W

E14

Oven

Dimmable



8711500038715



Special-purpose appliance bulb

Philips oven lamps can be used in ovens, rotisseries and similar places subject to high operating temperatures. Available for specific oven luminaires fitted in different positions, such as downlighters, side-lights and backlights.

Special-purpose lighting

- For specific applications
- For use in ovens

Highlights

For specific applications



Philips special-purpose incandescent light lamps are meant to be used for

specific applications. Light lamps for general home lighting are available in the Philips halogen, energy-saving and LED ranges.

For use in ovens



This Philips appliance lamp is specifically designed for use in ovens, resisting high heat up to 300 degrees Celcius.

Specifications

Characteristics

- Shape: Appliance
- Dimmable: Yes
- Socket: E14

Lamp dimensions

- Height: 57 mm
- Width: 25 mm

Durability

- Average life (at 2.7 hrs/day): 1 a
- Nominal lifetime: 1,000 h

Light characteristics

- Application: Special application
- Colour rendering index (CRI): 100
- Colour temperature: 2700 K
- Nominal luminous flux: 165 lm

Power consumption

- Voltage: 230-240 V
- Wattage: 26 W
- Energy efficiency label (EEL): G

Technical specifications

- Chromaticity coordinate Y: 0.411
- Chromaticity coordinate X: 0.46



Issue date: 2023-11-08
Version: 0.687

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com