



PHILIPS
LED
Luster
3 W (20 W)
E27 cap
Cool daylight
Frosted

8718696564530

State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting

Sustainable choice

- Safe for any room and convenient to recycle

Beacon of trust

- You can trust what the Philips packaging is saying

Create a warm atmosphere

- High color rendering (CRI $>$ 80) for vivid colors

PHILIPS

Light beyond illumination

- Instant light when switched on

Highlights

No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them safe for any room and convenient to recycle.

Reliable quality

Philips keeps their promises about LED light performance. You can trust what the Philips packaging is saying about light output, lifetime, and wattage equivalent to incandescent lamps.

High color rendering (CRI > 80)



The color rendering index (CRI) is used to describe the effect of a light source

on color appearance. Natural outdoor light has a CRI of 100 and is used as the standard of comparison for any other light source. The CRI of Philips LED light bulbs is always higher than 80, close to the sun's value, reflecting colors truly and naturally.

Instant light when switched on

No need to wait: Philips LED light bulbs provide their full level of brightness immediately upon switching on.

Specifications

Bulb characteristics

- Shape: Luster
- Dimmable: No
- Socket: E27

Bulb dimensions

- Height: 79 mm
- Width: 45 mm

Durability

- Average life (at 2.7 hrs/day): 10 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 10,000 hour(s)
- Number of switch cycles: 30,000

Light characteristics

- Application: Soft light
- Beam angle: 150 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 200 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 25 mA
- Mercury content: 0 mg

Packaging information

- Product family: EyeComfort

Power consumption

- Power consumption per 1000h: 3 kW
- Power factor: 0.4
- Voltage: 220–240 V
- Wattage: 3 W
- Wattage equivalent: 20 W

Rated values

- Rated beam angle: 150 degree(s)
- Rated lifetime: 10,000 hour(s)
- Rated luminous flux: 200 lumen
- Rated power: 3 W

Packaging dimensions & weight

- SAP EAN/UPC – Piece: 8718696564530
- EAN/UPC – Case: 8718696564547
- SAP Gross Weight EAN (Piece): 0.049 kg
- Net Weight (Piece): 0.034 kg
- SAP Height (Piece): 9.600 cm
- SAP Length (Piece): 4.600 cm
- SAP Width (Piece): 4.600 cm



Issue date: 2019-08-05
Version: 0.260

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com