

# PHILIPS

Luster

LED

3 W (20 W)

E27 cap

Cool daylight

Frosted

8718696564530



## State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting

### **Beacon of trust**

- You can trust what the Philips packaging is saying

### **Create a warm atmosphere**

- High color rendering (CRI  $>$  80) for vivid colors

### **Choose for a sustainable solution**

- Safe for any room and convenient to recycle

### **Light beyond illumination**

- Instant light when switched on

# Highlights

## Reliable quality

Philips keeps their promises about LED light performance. You can trust what the Philips packaging is saying about light output, lifetime, and wattage equivalent to incandescent lamps.

## High color rendering (CRI > 80)



The color rendering index (CRI) is used to describe the effect of a light source on color appearance. Natural outdoor light has a CRI of 100 and is used as the standard of comparison for any other light source. The CRI of Philips LED light bulbs is always higher than 80, close to the sun's value, reflecting colors truly and naturally.

## No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them safe for any room and convenient to recycle.

## Instant light when switched on

No need to wait: Philips LED light bulbs provide their full level of brightness immediately upon switching on.

# Specifications

## Characteristics

- Shape: Luster
- Dimmable: No
- Lamp shape: Non directional luster
- Socket: E27

## Bulb dimensions

- Height: 7.9 cm
- Width: 4.5 cm

## Durability

- Average life (at 2.7 hrs/day): 10 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 10,000 hour(s)
- Number of switch cycles: 30,000

## Light characteristics

- Application: Soft light
- Beam angle: 150 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 200 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 25 mA

## Packaging information

- Product family: EyeComfort

#### Power consumption

- Power factor: 0.4
- Voltage: 220–240 V
- Wattage: 3 W
- Wattage equivalent: 20 W

#### Product dimensions & weight

- Length: 8 cm

#### Rated values

- Rated beam angle: 150 degree(s)
- Rated lifetime: 10,000 hour(s)
- Rated luminous flux: 200 lumen
- Rated power: 3 W

#### Technical specifications

- Frequency: 50 to 60

#### Packaging dimensions and weight

- EAN/UPC - product: 8718696564530
- Net weight: 0.034 kg
- Gross weight: 0.049 kg
- Height: 9.600 cm
- Length: 4.600 cm
- Width: 4.600 cm
- Material number (12NC):  
929001160408



Issue date: 2020-11-12  
Version: 0.533

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)