

PHILIPS

Globe

LED

8.5 W (70W)

E27 cap

Cool daylight

Frosted

8718696567135



Perfect long lasting LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your clear incandescent bulbs.

Create a warm atmosphere

- High color rendering (CRI \geq 80) for vivid colors

Innovative design

- long lifetime

Easy to enjoy

- Avoid the hassle of changing bulbs

Light beyond illumination

- Instant light when switched on

Highlights

High color rendering (CRI>80)



The color rendering index (CRI) is used to describe the effect of a light source

on color appearance. Natural outdoor light has a CRI of 100 and is used as the standard of comparison for any other light source. The CRI of Philips LED light bulbs is always higher than 80, close to the sun's value, reflecting colors truly and naturally.

Lifetime 15

Providing the same incandescent look and feel, while offering the much longer lifetime.

Avoid the hassle of changing

The durable alternative to incandescent light bulbs, Philips LED bulbs can be installed and forgotten about, maintaining their beautiful light beam for years and years to come.

Instant light when switched on

No need to wait: Philips LED light bulbs provide their full level of brightness immediately upon switching on.

Specifications

Bulb characteristics

- Dimmable: No
- Lamp shape: Non directional globe
- Socket: E27

Bulb dimensions

- Height: 12.8 cm
- Width: 9.5 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Application: Soft light
- Beam angle: 150 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Light Color Category: Cool Daylight, Warm White
- Nominal luminous flux: 806 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Other characteristics

- Lamp current: 45 mA

Power consumption

- Power factor: 0.7
- Voltage: 220–240 V
- Wattage: 8.5 W
- Wattage equivalent: 70 W

Product dimensions & weight

- Length: 12.8 cm

Rated values

- Rated beam angle: 150 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 806 lumen
- Rated power: 8.5 W

Technical specifications

- Frequency: 50–60 Hz

Packaging dimensions and weight

- EAN/UPC – product: 8718696567135
- Net weight: 0.130 kg
- Gross weight: 0.190 kg
- Height: 16.100 cm
- Length: 9.600 cm
- Width: 9.600 cm
- Material number (12NC): 929001229307



Issue date: 2023-11-08
Version: 0.563

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com