

# PHILIPS

Bulb (Dimmable)


LED

6W (60W)


E27

Warm white

Dimmable



8718696574737



## Designed to be seen

Familiar shapes you know and love. They use around 80% less energy than traditional light bulbs thanks to the latest LED energy-saving technology and last ten times longer

### Save on energy

- Saves up to 80% energy

### Designed for perfect light quality

- Vintage style, modern LED technology

### High quality light

- Omni-directional light

### Create desired ambiance

- Dimmable\*\*\*

# Highlights

## Saves up to 80% energy



Save up to 80% energy compared to your standard bulb. It pays for itself and saves you money year after year. So reduce your energy bill and start saving Now.

## LEDClassic (filament)

LED Classic bulbs are based on standard LED energy-saving technology, except the LEDs are arranged in such a way as to mimic classic incandescent bulbs. Now you can enjoy this retro-style bulb with state-of-the-art technology.

## Omni-directional light

This innovative lens delivers omni-directional light distribution, preventing the shadow that normally appears at the beam spread edge. The result? Natural, warm white light all around.

## Dimmable\*\*\*



0% 100%

This lamp can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels.

# Specifications

## Characteristics

- Shape: Bulb
- Dimmable: Yes
- Lamp shape: Non directional bulb
- Socket: E27

## Bulb dimensions

- Height: 112 mm
- Width: 60 mm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

## Light characteristics

- Application: Comfortable light, General light
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 806 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Other characteristics

- Lamp current: 40 mA

## Packaging information

- Product family: LED Classic

## Power consumption

- Power factor: 0.7
- Voltage: 220-240 V
- Wattage: 7.5 W
- Wattage equivalent: 70 W

## Rated values

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 806 lumen
- Rated power: 7.5 W

## Packaging dimensions and weight

- EAN/UPC - product: 8718696574737
- Net weight: 0.030 kg
- Gross weight: 0.052 kg
- Height: 12.000 cm
- Length: 6.600 cm
- Width: 6.600 cm
- Material number (12NC): 929001228008



Issue date: 2021-09-17  
Version: 0.463

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)