



PHILIPS
LED
Bulb (Dimmable)
7.5W (60W)
E27
Flame
Dimmable



8718696574836

Designed to be seen

Familiar shapes you know and love. They use around 80% less energy than traditional light bulbs thanks to the latest LED energy-saving technology and last ten times longer

Save on energy

- Saves up to 80% energy

Create a warm atmosphere

- Extra warm light 2000K

Designed for perfect light quality

- Vintage style, modern LED technology
- Omni-directional light

PHILIPS

Highlights

Saves up to 80% energy



Save up to 80% energy compared to your standard bulb. It pays for itself and saves you money year after year.

So reduce your energy bill and start saving Now.

2000 K [LED]

Light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, more cozy light, while those with a higher Kelvin value produce a cool, more energizing light.

LEDClassic (filament)

LED Classic bulbs are based on standard LED energy-saving technology, except the LEDs are arranged in such a way as to mimic classic incandescent bulbs. Now you can enjoy this retro-style bulb with state-of-the-art technology.

Omni-directional light

This innovative lens delivers omni-directional light distribution, preventing the shadow that normally appears at the beam spread edge. The result? Natural, warm white light all around.

Specifications

Bulb characteristics

- Shape: Bulb
- Dimmable: Yes
- Socket: E27

Bulb dimensions

- Height: 112 mm
- Width: 60 mm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

Light characteristics

- Application: Comfortable light, Soft light, General light
- Color rendering index (CRI): 80
- Color temperature: 2000 K
- Light Color Category: Flame
- Nominal luminous flux: 600 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Other characteristics

- Lamp current: 42 mA
- Mercury content: 0 mg

Packaging information

- Product family: LED Classic

Power consumption

- Energy efficiency label: A+
- Power consumption per 1000h: 8 kW
- Power factor: 0.7
- Voltage: 220-240 V
- Wattage: 7.5 W
- Wattage equivalent: 60 W
- Energy Efficiency Label: A+

Rated values

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 600 lumen
- Rated power: 7.5 W

Packaging dimensions & weight

- SAP EAN/UPC - Piece: 8718696574836
- EAN/UPC - Case: 8718696574843
- SAP Gross Weight EAN (Piece): 0.052 kg
- Net Weight (Piece): 0.030 kg
- SAP Height (Piece): 12.000 cm
- SAP Length (Piece): 6.600 cm
- SAP Width (Piece): 6.600 cm



Issue date: 2019-05-07
Version: 0.288

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com