



PHILIPS  
LED  
Bulb (Dimmable)  
7W (60W)  
E27  
Flame  
Dimmable



8718696574935

## Designed to be seen

Familiar shapes you know and love. They use around 80% less energy than traditional light bulbs thanks to the latest LED energy-saving technology and last ten times longer

### Save on energy

- Saves up to 80% energy

### Create a warm atmosphere

- Extra warm light 2000K

### Designed for perfect light quality

- Vintage style, modern LED technology

### High quality light

- Omni-directional light

# PHILIPS

# Highlights

## Saves up to 80% energy



Save up to 80% energy compared to your standard bulb. It pays for itself and saves you money year after year.

So reduce your energy bill and start saving Now.

### 2000 K [LED]

Light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, more cozy light, while those with a higher Kelvin value produce a cool, more energizing light.

### LEDClassic (filament)

LED Classic bulbs are based on standard LED energy-saving technology, except the LEDs are arranged in such a way as to mimic classic incandescent bulbs. Now you can enjoy this retro-style bulb with state-of-the-art technology.

### Omni-directional light

This innovative lens delivers omni-directional light distribution, preventing the shadow that normally appears at the beam spread edge. The result? Natural, warm white light all around.

# Specifications

## Bulb characteristics

- Shape: Globe
- Dimmable: Yes
- Socket: E27

## Bulb dimensions

- Height: 188 mm
- Width: 125 mm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

## Light characteristics

- Application: Comfortable light, Soft light, General light
- Color rendering index (CRI): 80
- Color temperature: 2000 K
- Light Color Category: Flame
- Nominal luminous flux: 600 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Other characteristics

- Lamp current: 40 mA
- Mercury content: 0 mg

## Packaging information

- Product family: LED Classic

## Power consumption

- Power consumption per 1000h: 7 kW
- Power factor: 0.7
- Voltage: 220-240 V
- Wattage: 7 W
- Wattage equivalent: 60 W
- Energy Efficiency Label: A+

## Rated values

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 600 lumen
- Rated power: 7 W

**Packaging dimensions and weight**

- EAN/UPC - product: 8718696574935
- Net weight: 0.115 kg
- Gross weight: 0.217 kg
- Height: 19.600 cm
- Length: 12.800 cm
- Width: 12.800 cm
- SAP EAN/UPC - Piece: 8718696574935
- Material number (12NC): 929001229108
- EAN/UPC - Case: 8718696574942
- SAP Gross Weight EAN (Piece): 0.217 kg
- Net Weight: 0.115 kg
- SAP Height (Piece): 19.600 cm
- SAP Length (Piece): 12.800 cm
- SAP Width (Piece): 12.800 cm



Issue date: 2020-04-06  
Version: 0.432

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)