



PHILIPS  
LED  
Candle (Dimmable)  
4.5W (40W)  
B22  
Warm white  
Dimmable



8718696576038

## Designed to be seen

Familiar shapes you know and love. They use around 80% less energy than traditional light bulbs thanks to the latest LED energy-saving technology and last ten times longer.

### Save on energy

- Saves up to 80% energy

### Designed for perfect light quality

- Vintage style, modern LED technology
- Omni-directional light

### Create desired ambiance

- Dimmable\*\*\*

# PHILIPS

# Highlights

## Saves up to 80% energy



Save up to 80% energy compared to your standard bulb. It pays for itself and saves you money year after year. So reduce your energy bill and start saving Now.

## LEDClassic (filament)

LED Classic bulbs are based on standard LED energy-saving technology, except the LEDs are arranged in such a way as to mimic classic incandescent bulbs. Now you can enjoy this retro-style bulb with state-of-the-art technology.

## Omni-directional light

This innovative lens delivers omni-directional light distribution, preventing the shadow that normally appears at the beam spread edge. The result? Natural, warm white light all around.

## Dimmable\*\*\*



This lamp can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels.

# Specifications

## Bulb characteristics

- Shape: Luster
- Socket: B22

## Bulb dimensions

- Height: 87.5 mm
- Width: 45 mm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 15,000 h
- Number of switch cycles: 20,000

## Light characteristics

- Application: General light, Decorative light
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 470 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Other characteristics

- Lamp current: 29 mA
- Mercury content: 0 mg

## Power consumption

- Energy efficiency label: A++
- Power consumption per 1000h: 5 kW
- Voltage: 220-240 V
- Wattage: 4.5 W
- Wattage equivalent: 40 W
- Energy Efficiency Label: A++

## Rated values

- Rated lifetime: 15,000 h
- Rated luminous flux: 470 lumen
- Rated power: 4.5 W

## Packaging dimensions & weight

- EAN/UPC - Piece: 8718696576038
- EAN/UPC - Case: 8718696576045
- Weight product including package: 0.035 kg
- Weight product without package: 0.011 kg
- SAP Height (Piece): 16.600 cm
- SAP Length (Piece): 5.200 cm
- SAP Width (Piece): 10.000 cm



Issue date: 2019-04-01  
Version: 0.278

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)