

PHILIPS

Spot

LED

5W (50W)

GU5.3 cap

Warm white

Non-dimmable



8718696579558



Durable LED accent lighting with a focused beam

Philips LED spots provide a focused bright beam, an long life, and significant energy savings.

Beacon of trust

- You can trust what the Philips packaging is saying.

Simple replacement

- Get maximum light output as soon as you flip the switch.

Create a warm atmosphere

- True incandescent-like warm white light (2700 K)

Choose for a sustainable solution

- Safe for any room and convenient to recycle

Highlights

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

Instant start

Immediate light when switching on, that is the promise of the Philips instant starting energy saving LED lamps.

Warm white light (2700K)

Light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, more cozy light, while those with a higher Kelvin value produce a cool, more energizing light.

No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them safe for any room and convenient to recycle.

Specifications

Bulb characteristics

- Shape: Spot
- Dimmable: No
- Lamp shape: Directional spot
- Socket: GU5.3

Bulb dimensions

- Height: 46 mm
- Width: 50 mm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Application: Accent light
- Beam angle: 24 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 400 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Other characteristics

- Lamp current: 580 mA
- Efficacy: 80 lm/W

Power consumption

- Power factor: >0.5
- Voltage: 12 V
- Wattage: 5 W
- Wattage equivalent: 50 W

Product dimensions & weight

- Length: 4.7 cm

Rated values

- Rated beam angle: 24 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 400 lumen
- Rated peak intensity: 1700 cd
- Rated power: 5 W

Technical specifications

- Frequency: 50-60 Hz

Bulb characteristics

- Shape: Spot
- Application: Accent light
- EAN/UPC - product: 8718696579558
- Rated beam angle: 24 degree(s)
- Height: 46 mm
- Average life (at 2.7 hrs/day): 15 year(s)
- Beam angle: 24 degree(s)
- Lamp current: 580 mA
- Net weight: 0.045 kg
- Rated lifetime: 15,000 hour(s)
- Lumen maintenance factor: 0.7
- Gross weight: 0.052 kg
- Rated luminous flux: 400 lumen
- Lamp shape: Directional spot
- Width: 50 mm
- Color rendering index (CRI): 80
- Height: 5.500 cm
- Rated peak intensity: 1700 cd
- Socket: GU5.3
- Number of switch cycles: 50,000
- Color temperature: 2700 K
- Length: 4.500 cm
- Power factor: >0.5
- Rated power: 5 W
- Light Color Category: Warm White
- Width: 4.500 cm
- Voltage: 12 V
- Nominal luminous flux: 400 lumen
- Material number (12NC): 929001240108
- Wattage: 5 W
- Length: 4.7 cm
- Starting time: <0.5 s
- Wattage equivalent: 50 W
- Warm-up time to 60% light: Instant full light
- Frequency: 50-60 Hz



Issue date: 2022-06-12
Version: 0.520

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com