



PHILIPS  
LED  
Luster  
4 W (40 W)  
E14 cap  
White

8718696597859

## Warm white light, no compromise on light quality

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

### Create a warm atmosphere

- True incandescent-like warm white light (2700 K)

### Pure and elegant design

- Perfect fit and high quality finishing

# PHILIPS

**Designed for perfect light quality**

- High color rendering (CRI  $\geq$  80) for vivid colors

# Highlights

## Warm white light (2700K)

Light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, more cozy light, while those with a higher Kelvin value produce a cool, more energizing light.

## Beautiful, switched on an off

Familiar shapes are a perfect fit for your fixtures: we have retained the shapes and appearance of the classic light bulb.

## High color rendering (CRI>80)



The color rendering index (CRI) is used to describe the effect of a light source on color appearance. Natural outdoor

light has a CRI of 100 and is used as the standard of comparison for any other light source. The CRI of Philips LED light bulbs is always higher than 80, close to the sun's value, reflecting colors truly and naturally.

# Specifications

## Bulb characteristics

- Shape: Luster
- Dimmable: No
- Socket: E14

## Bulb dimensions

- Height: 86 mm
- Width: 45 mm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Application: Basic light
- Beam angle: 180 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: White
- Nominal luminous flux: 350 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 40 mA
- Mercury content: 0 mg

## Packaging information

- Product family: EyeComfort

## Power consumption

- Power consumption per 1000h: 4 kW
- Power factor: 0.4
- Voltage: 220-240 V
- Wattage: 4 W
- Wattage equivalent: 40 W

## Rated values

- Rated beam angle: 180 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 350 lumen
- Rated power: 4 W

## Packaging dimensions & weight

- SAP EAN/UPC – Piece: 8718696597859
- EAN/UPC – Case: 8718696597866
- SAP Gross Weight EAN (Piece): 0.049 kg
- Net Weight (Piece): 0.034 kg
- SAP Height (Piece): 9.600 cm
- SAP Length (Piece): 4.600 cm
- SAP Width (Piece): 4.600 cm



Issue date: 2019-07-04  
Version: 0.208

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)