

PHILIPS

Bulb


LED

8 W (60 W)

E27

Cool White/ Warm White

One bulb
two light colors



8718696598375



One lamp. Your switch. Two colour settings.

Change your room ambiance to suit whatever you're doing. With the Philips SceneSwitch LED bulb, you can easily change the setting from warm bright light to a cool and energising light. All you need is your existing switch.

High-quality light

- Learn about light
- Designed for the comfort of your eyes

Choose for a sustainable solution

- Long-life bulbs – Last up to 15 years
- Better for your wallet and your planet

Light beyond illumination

- No dimmer or additional installation needed
- Restore the lamp to the default factory setting
- Light colour changes at the flick of the existing wall switch

Highlights

Learn about light



Colour temperature: light can have different colour temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more tranquil light, while those with a higher Kelvin value produce a cool, more energising light. CRI: the colour rendering index (CRI) is used to describe the effect of a light source on colour appearance. Natural sunlight has a CRI of 100. The CRI of Philips LED lamps is always higher than 80, which ensures that colours are shown as true and natural.

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

15,000-hour rated average life




With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Saves up to 80% energy



LED technology saves up to 80% energy compared to your standard bulb. It therefore pays for itself and saves you money year after year. It also helps to protect the environment.

Plug and play



Delivers a variety of great light scenes straight out of the box to suit your different needs and moods. The intelligence is in the lamp itself, so no dimmer or other additional installation is required. Simply replace your lamp with this Scene Switch lamp, and you can change between different scenes at a flick of your existing wall switch. Lowest level of investment and effort required to enjoy the highest level of comfort. Now you can change the ambience easily to suit whatever you're doing and your mood at the time.

Reset (Sceneswitch)



If multiple lamps are used and they are no longer synchronised, simply toggle the switch (turn it on and off again within 1 second) to restore the lamps to the default factory setting.

Two light colours (SceneSwitch)

Flick the switch to change the ambience from a light that is similar to natural daylight to a warm, cosy light that helps you relax and enjoy the moment. Now you can easily customise your room for a variety of activities or adapt it to suit your mood.

Specifications

Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Technology: LED
- Type of glass: Frosted

Lamp dimensions

- Height: 11.1 cm
- Weight: 0.052 kg
- Width: 6.1 cm

Durability

- Average life (at 2.7 hrs/day): 15 a
- Lumen maintenance factor: 0.7
- Nominal lifetime: 15,000 h
- Number of switch cycles: 100,000

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2700/4000 K
- Light Colour Category: Cool White/
Warm White
- Nominal luminous flux: 806 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant
full light

Other characteristics

- Lamp current: 78 mA
- Efficacy: 100 lm/W

Packaging information

- Product family: SceneSwitch,
EyeComfort

Power consumption

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage: 8 W
- Wattage equivalent: 60 W
- Energy efficiency label (EEL): A+

Product dimensions and weight

- Length: 11.1 cm

Rated values

- Rated lifetime: 15,000 h
- Rated luminous flux: 806 lm
- Rated power: 8 W

Technical specifications

- Frequency: 50–60 Hz



Issue date: 2023-11-08
Version: 0.696

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com