

PHILIPS

Candle & Lustre

LED

5.5W-40W

E14

Warm/Extra Warm/Very Warm

Non-dimmable



8718696598474



One lamp. Your switch. Three light settings.

Change your room ambiance to suit whatever you're doing. With the Philips SceneSwitch LED lamp, you can easily change the setting from bright light, to natural light and to a cozy warm glow. All you need is your existing switch.

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

Light beyond illumination

- Restore the lamp to the default factory setting
- No dimmer or additional installation needed
- The lamp can memorize your last setting



Highlights

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Plug and play



Does not require any additional installation or a dimmer switch. This bulb is not suitable for use with dimmers. If used on a dimmer set the dimmer setting to 100% brightness.

Auto memory (sceneswitch)



This Scene Switch lamp has a built-in memory chip which will memorize your last light setting if the switch is turned off for longer than 6 seconds. If you don't often switch between activities, the light will be in your favorite mode when you turn it on again.

Reset (Sceneswitch)



If multiple lamps are used and they are no longer synchronized, simply toggle the switch (turn it on and off again within 1 second) to restore the lamps to the default factory setting.

Specifications

Characteristics

- Shape: Candle
- Dimmable: No
- Lamp shape: Non directional candle
- Socket: E14

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 100,000

Bulb dimensions

- Height: 11.3 cm
- Width: 3.8 cm

Light characteristics

- Application: Soft light
- Color rendering index (CRI): 80
- Color temperature: 2700-2500-2200 K
- Light Color Category: Warm/Very Warm/Extra Warm
- Nominal luminous flux: 470-190-50 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp Classification Risk Group: RG1
- Lamp current: 50 mA

Packaging information

- Product family: SceneSwitch, EyeComfort

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 5.5, 4, 2 W
- Wattage equivalent: 40 W
- Energy Efficiency Label (EEL): A+

Product dimensions & weight

- Length: 11.3 cm

Rated values

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 470-190-50 lumen
- Rated power: 5.5-4-2 W

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718696598474
- Net weight: 0.068 kg
- Gross weight: 0.089 kg
- Height: 16.600 cm
- Length: 4.200 cm
- Width: 10.000 cm
- Material number (12NC): 929001260858



Issue date: 2023-11-07
Version: 0.683

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com